

TS35 64 KLIPPON K4K11

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



Similar to illustration

The system accessories for the Klippon® K enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35 and TS15
- Mounting plates
- Hinges
- Wall-mounted holder

Weidmüller can manufacture and supply this enclosure - according to customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

| | |
|------------|--|
| Version | Rail, TS 35, TS 35 x 7.5, Width: 64 mm, without slot, Steel, galvanized, chromium-plated |
| Order No. | 1910060000 |
| Type | TS35 64 KLIPPON K4K11 |
| GTIN (EAN) | 4032248536979 |
| Qty. | 1 items |

TS35 64 KLIPPON K4K11

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 7.5 mm | Depth (inches) | 0.2953 inch |
| Height | 35 mm | Height (inches) | 1.378 inch |
| Width | 64 mm | Width (inches) | 2.5197 inch |
| Net weight | 24 g | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General information

| | | | |
|--------------------|--------------|---------------------|-----------------------------|
| Material thickness | 1 mm | Installation advice | Direct mounting |
| Standards | DIN EN 60715 | Surface finish | galvanized, chromium-plated |
| Impact resistance | 10.00 J | Basic material | Steel |
| Stamp dimensions | 5.5 x 20 mm | | |

General information on accessories

| | | | |
|--------------------|-------|------------------|-----------------------------|
| Material thickness | 1 mm | Surface finish | galvanized, chromium-plated |
| Basic material | Steel | Stamp dimensions | 5.5 x 20 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001285 | ETIM 9.0 | EC001285 |
| ETIM 10.0 | EC001285 | ECLASS 14.0 | 27-40-06-02 |
| ECLASS 15.0 | 27-40-06-02 | | |