

ETO CC 15/49 TRANSPAR.

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

General ordering data

| | |
|------------|--|
| Version | ClipCard, Accessories, 15 x 49 mm, Transparent |
| Order No. | 1880830000 |
| Type | ETO CC 15/49 TRANSPAR. |
| GTIN (EAN) | 4032248480906 |
| Qty. | 10 items |

ETO CC 15/49 TRANSPAR.

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 1 mm | Depth (inches) | 0.0394 inch |
| Height | 15 mm | Height (inches) | 0.5906 inch |
| Width | 49 mm | Width (inches) | 1.9291 inch |
| Net weight | 11.7 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | |
|--------------------------------------|-----------------------------|-----------|
| Adhesive | Permanent acrylic copolymer | |
| Number per sheet | 76 | |
| Version | Self-adhesive | |
| Width | 49 mm | |
| UL 94 flammability rating | V-2 | |
| Operating temperature range, max. | 100 °C | |
| Operating temperature range, min. | -40 °C | |
| Colour | Transparent | |
| Halogen | No | |
| Basic material | Polyester film | |
| Number of markers per packaging unit | Form of supply | MultiCard |
| Recommended industries | Machinery | |
| Number of markers per combination | 1 MultiCard = Accessories | |
| Operating temperature range | -40...100 °C | |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ETIM 10.0 | EC001288 | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 | | |

ETO CC 15/49 TRANSPAR.

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

