

**SCREWTY SET****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The ideal tool for any application

Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

**General ordering data**

Version	Cable gland tool for M8, M12 lines and connectors
Order No.	<a href="#">1910000000</a>
Type	SCREWTY SET
GTIN (EAN)	4032248436842
Qty.	1 items
Packaging	Cardboard box

## SCREWTY SET

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	190.08 g
------------	----------

## Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

## Technical data

Description of article	Screwed gland tool for M8, M12-cables and connectors
------------------------	--

## Important note

Product information	Included in delivery: <ul style="list-style-type: none"> <li>• Standard handle 1/4 inch</li> <li>• Attachment M8 for moulded lines</li> <li>• Attachment M8F for customisable connectors</li> <li>• Attachment M12 for moulded lines</li> <li>• Attachment M12F for customisable connectors</li> </ul>
---------------------	--

## Classifications

ETIM 8.0	EC000149	ETIM 9.0	EC000149
ETIM 10.0	EC000149	ECLASS 14.0	21-01-90-90
ECLASS 15.0	21-01-90-90		

**SCREWTY SET**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Accessories**

**Screwty for M23 moulded cables and customisable connectors**



The Screwty® attachment is suitable for customisable M23 round plug-in connectors and for overmoulded M23 round plug-in connectors, with an outside dimension of the knurled nut of  $26.2 \pm 0.3$  mm. The tightening torque is 2-2.5 Nm.

**General ordering data**

Type	SCREWTY M23	Version	
Order No.	<a href="#">1981560000</a>		Cable gland tool adapter for M23 lines and connectors
GTIN (EAN)	4032248677702		
Qty.	1 ST		

**Screwty for M12 K-coded and L-coded overmolded cables**



Weidmüller offers a wide range of tools and accessories for sensor-actuator cabling.

**General ordering data**

Type	SCREWTY M12 K+L 2.5 O.SD	Version	
Order No.	<a href="#">2522710000</a>		Cable gland tool adapter for moulded M12 lines, K- and L-coded
GTIN (EAN)	4050118534566		
Qty.	1 ST		
Type	SCREWTY M12 K+L O.SD	Version	
Order No.	<a href="#">2486610000</a>		Cable gland tool adapter for moulded M12 lines, K- and L-coded
GTIN (EAN)	4050118497403		
Qty.	1 ST		