

**IE-PH-V05M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



HDC plug-in connector according to IEC 61076-3-106  
ver.5 in metal, empty housing

**General ordering data**

Version	Empty enclosure, Plug housing, Variant 5 to IEC 61076-3-106, IP67
Order No.	<a href="#">1962540000</a>
Type	IE-PH-V05M
GTIN (EAN)	4032248644674
Qty.	10 items

## IE-PH-V05M

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E316369

## Dimensions and weights

Depth	78 mm	Depth (inches)	3.0709 inch
Height	26.7 mm	Height (inches)	1.0512 inch
Width	26.7 mm	Width (inches)	1.0512 inch
Net weight	76.9 g		

## Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6bl, 6c
REACH SVHC	Lead 7439-92-1
SCIP	4f3aae94-c2bc-4010-b63b-5b114ba6bd55

## General data

Colour	Miscellaneous	Housing main material	diecast aluminium
Protection degree	IP67	Plugging cycles	750

## General standards


Connector standard	IEC 61076-3-106 Var. 5	Certificate no. (cULus)	E316369
--------------------	------------------------	-------------------------	---------

## Classifications

ETIM 8.0	EC001031	ETIM 9.0	EC001031
ETIM 10.0	EC001031	ECLASS 14.0	27-19-01-04
ECLASS 15.0	27-19-01-04		

**Drawings**

**Dimensioned drawing**



## IE-PH-V05M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## RJ45



RJ45 inserts for plug-in connectors ver.1 / 4 / 5 / 14, HDC and junction boxes IE-OM...; IE-OP...; IE-CC...

## General ordering data

Type	IE-PI-RJ45-FH	Version
Order No.	<a href="#">1962730000</a>	Plug insert RJ45 IDC, Plug insert RJ45, no tools required, TIA-568A,
GTIN (EAN)	4032248654017	EIA/TIA T568 B, PROFINET
Qty.	10 ST	
Type	IE-PI-RJ45-TH	Version
Order No.	<a href="#">1962720000</a>	Plug insert RJ45 IDC, Plug insert RJ45, crimp
GTIN (EAN)	4032248644834	
Qty.	10 ST	

## Dust caps



For protecting your devices against dust and dirt.

## General ordering data

Type	IE-PP-V05M	Version
Order No.	<a href="#">1968920000</a>	Flange-mounted housing, protective cap
GTIN (EAN)	4032248692668	
Qty.	10 ST	

## Empty housings



HDC plug-in connector according to IEC 61076-3-106 ver.5 in metal, empty housing

## Accessories

### General ordering data

Type	IE-PH-AD-V05M-RJ45	Version	
Order No.	<a href="#">1993540000</a>	Spare insert holder, Variant 5 to IEC 61076-3-106	
GTIN (EAN)	4050118378610		
Qty.	1 ST		