

IE-BHD-V04P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



PushPull plug-in connector according to IEC
61076-3-106 ver.4 (IEC24702), plastic, empty housing

General ordering data

Version	Device flange, Variant 4 to IEC 61076-3-106, IP67
Order No.	2027660000
Type	IE-BHD-V04P
GTIN (EAN)	4050118406061
Qty.	200 items

IE-BHD-V04P

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E471884

Dimensions and weights

Depth	15.5 mm	Depth (inches)	0.6102 inch
Height	22.3 mm	Height (inches)	0.878 inch
Width	32 mm	Width (inches)	1.2598 inch
Wall thickness, max.	3.5 mm	Net weight	3.73 g

Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

General data

UL 94 flammability rating	V-0	Colour	Miscellaneous
Housing main material	PA UL 94 V0	Protection degree	IP67

General standards


Connector standard	IEC 61076-3-106 Var. 4	Certificate no. (cULus)	E471884
--------------------	------------------------	-------------------------	---------

Classifications


ETIM 8.0	EC001031	ETIM 9.0	EC001031
ETIM 10.0	EC001031	ECLASS 14.0	27-19-01-04
ECLASS 15.0	27-19-01-04		

Drawings

Drawing




Installation cut-out



max. Paneldicke: 3,5mm
max. Panel thickness: 3,5 mm

M2,5 Gewinde darf kein Sackloch sein
M2.5 threads mustn't go through the panel

Blank

ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	ESG 9/11 K MC NE WS	Version	
Order No.	1857440000		ESG, Device markers x 11 mm, PA 66, Colour: white, Self-adhesive
GTIN (EAN)	4032248402731		
Qty.	200 ST		