

## LOGIC UNIT WCU 650

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



With the fully encapsulated WCU 501 and WCU 650 logic modules, you monitor, control and regulate your processes - even under extreme environmental conditions. In this regard, the WCU series offers optimum dimensions, performance, robustness and user-friendliness. The graphic and intuitive Micon-L programming environment enables flexible switching of the analogue and digital inputs, plus the digital outputs too. The scope of both the software and the hardware can be expanded to suit customer requirements upon request. .

## General ordering data

Version	graphically programmable logic module, CAN interface, Mounting foot
Order No.	<a href="#">2010680000</a>
Type	LOGIC UNIT WCU 650
GTIN (EAN)	4050118397406
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2024-06-30T00:00:00+02:00
Alternative product	<a href="#">LOGIC UNIT WCU 860S</a>

## LOGIC UNIT WCU 650

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

## Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E141197

## Dimensions and weights

Depth	30 mm	Depth (inches)	1.1811 inch
Height	93 mm	Height (inches)	3.6614 inch
Width	45 mm	Width (inches)	1.7716 inch
Net weight	102 g		

## Temperatures

Storage temperature	-40 °C...70 °C	Operating temperature	-40 °C...70 °C
Humidity	5 - 95% rel. humidity		

## Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

## Connection data

Type of connection	Plug-in spring-type terminals (0.25 - 1.5 mm <sup>2</sup> )
--------------------	---

## General data

Vibration resistance	min. 50 m/s <sup>2</sup> (5 g) @ 10...150 Hz	Mounting rail	TS 35
----------------------	--	---------------	-------

## Power supply

Reverse polarity protection	yes (combined with external fuse)
-----------------------------	-----------------------------------

## System data

Interface	TTL 232
-----------	---------

## Classifications

ETIM 8.0	EC001417	ETIM 9.0	EC001417
ETIM 10.0	EC001417	ECLASS 14.0	27-24-22-16
ECLASS 15.0	27-24-22-16		

## LOGIC UNIT WCU 650

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Starterkits



With the fully encapsulated WCU 501 and WCU 650 logic modules, you monitor, control and regulate your processes - even under extreme environmental conditions. In this regard, the WCU series offers optimum dimensions, performance, robustness and user-friendliness. The graphic and intuitive Micon-L programming environment enables flexible switching of the analogue and digital inputs, plus the digital outputs too. The scope of both the software and the hardware can be expanded to suit customer requirements upon request. .

## General ordering data

Type	STARTERKIT WCU 650	Version
Order No.	<a href="#">2007290000</a>	graphically programmable logic module incl. programming adapter,
GTIN (EAN)	4050118392517	CAN interface, Mounting foot
Qty.	1 ST	

## Accessories



With the fully encapsulated WCU 501 and WCU 650 logic modules, you monitor, control and regulate your processes - even under extreme environmental conditions. In this regard, the WCU series offers optimum dimensions, performance, robustness and user-friendliness. The graphic and intuitive Micon-L programming environment enables flexible switching of the analogue and digital inputs, plus the digital outputs too. The scope of both the software and the hardware can be expanded to suit customer requirements upon request. .

## General ordering data

Type	WCU 860S - MICON-L CABLE	Version
Order No.	<a href="#">2515020000</a>	USB 2.0
GTIN (EAN)	4050118528749	
Qty.	1 ST	