

HS 3.2-9.5/50 MM W

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

Version	Conductor and cable markers, 3.2 - 9.5 mm, 50.8 x 15.1 mm, white
Order No.	2437690000
Type	HS 3.2-9.5/50 MM W
GTIN (EAN)	4050118460742
Qty.	500 items

HS 3.2-9.5/50 MM W

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.77 mm	Depth (inches)	0.0303 inch
Height	50.8 mm	Height (inches)	2 inch
Width	15.1 mm	Width (inches)	0.5945 inch
Net weight	1.04 g		

Temperatures

Operating temperature range	-55...135 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Type of printing	neutral	Width	15.1 mm
Operating temperature range, max.	135 °C	Operating temperature range, min.	-55 °C
Colour	white	Halogen	Yes
Basic material	Polyolefine	Printed characters	without
Recommended industries	Plant manufacture, Energy, Device manufacturer, Machinery	compatible printer	THM MULTIMARK , THM MULTIMARK PLUS
Operating temperature range	-55...135 °C	Number per roll	500

Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	16 mm ²
Conductor cross-section, min.	4 mm ²	Conductor O.D., max.	9.5 mm
Conductor O.D., min.	3.2 mm	Rate of shrinkage	3:1
Recommended shrinking temperature	90 °C	Conductor O.D.	3.2 - 9.5 mm
Cross-section for connected wire	4 - 16 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

HS 3.2-9.5/50 MM W

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

