


**CMA-31-300-5A-5VA-0,5**
**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com


**Plug-on current transformers**

Plug-on current transformers are used wherever high currents of up to 5000A need to be measured and processed. Our plug-on current transformers supply secondary currents of 1A or 5A. Weidmüller also offers compact low-power current transformers to convert currents of up to 600 A to voltages of up to 333 mV.

**General ordering data**

Version	Primary current: 300 A, Secondary current max.: 5 A, Load: 5 VA, Tolerance class: 0,5, closed current transformer
Order No.	<a href="#">2420990000</a>
Type	CMA-31-300-5A-5VA-0,5
GTIN (EAN)	4050118429220
Qty.	1 items
Manufacturer	MBS AG

## CMA-31-300-5A-5VA-0,5

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	52 mm	Depth (inches)	2.0472 inch
Height	80.9 mm	Height (inches)	3.185 inch
Width	60 mm	Width (inches)	2.3622 inch
Net weight	281.6 g		

### Temperatures

Storage temperature	-25 °C...70 °C	Operating temperature	-5 °C...50 °C
---------------------	----------------	-----------------------	---------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

### Dimensions of live conductors

Type of conductor	Insulated conductor only	Round conductor	25.70 mm
Rail	20 x 20 mm, 25 x 12 mm, 30 x 10 mm	Installation location	Indoor use

### Electrical attributes

Tolerance class	0,5	Secondary current	0...5 A
Load	5 VA	Primary current	300 A

### Technical properties

Protection degree	IP20	Insulation class	E
Thermal rated continuous current I <sub>thermal</sub>	1.2 x I <sub>rated</sub>	Nominal frequency	50 Hz

### Insulation coordination

Standard	IEC 61869-1: 2007, IEC 61869-2: 2012	Tolerance class	0,5
----------	-----------------------------------------	-----------------	-----

### Classifications




ETIM 8.0	EC002048	ETIM 9.0	EC002048
ETIM 10.0	EC002048	ECLASS 14.0	27-21-09-02
ECLASS 15.0	27-21-09-02		

CMA-31-300-5A-5VA-0,5

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

Drawings

[www.weidmueller.com](http://www.weidmueller.com)



## CMA-31-300-5A-5VA-0,5

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

## Accessories

[www.weidmueller.com](http://www.weidmueller.com)

### Plug-on current transformer - ValueLine



#### Plug-on current transformers

Plug-on current transformers are used wherever high currents of up to 5000A need to be measured and processed. Our plug-on current transformers supply secondary currents of 1A or 5A. Weidmüller also offers compact low-power current transformers to convert currents of up to 600 A to voltages of up to 333 mV.

#### General ordering data

Type	CMA-31-41-SNAP-ON	Version	
Order No.	<a href="#">2723380000</a>		
GTIN (EAN)	4050118810622		
Qty.	1 ST		