

**PRO COM CAN OPEN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Weidmüller's plug-in communication modules enable individual components to exchange relevant data with the cloud. This lays the foundation for targeted process optimization using condition monitoring and remote controllability - factors that play a decisive role in increasing efficiency, quality, process stability and availability can contribute. The communication modules are designed according to IP20 protected, can be operated without tools and can be flexibly adapted to different customisable communication protocols.

**General ordering data**

Version	Communication module
Order No.	<a href="#">2467320000</a>
Type	PRO COM CAN OPEN
GTIN (EAN)	4050118482225
Qty.	1 items

## PRO COM CAN OPEN

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E258476
Certificate no. (cULusEX)	E470829

### Dimensions and weights

Depth	33.6 mm	Depth (inches)	1.3228 inch
Height	74.4 mm	Height (inches)	2.9291 inch
Width	35 mm	Width (inches)	1.378 inch
Net weight	75 g		

### Temperatures

Storage temperature	Operating temperature	-25 °C...70 °C
---------------------	-----------------------	----------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	1df9fee4-69cb-4b0a-a401-554c8cdbf60e

### General data

Weight	36 g	
Protection degree	IP20	
MTTF	According to Standard	SN 29500
	Operating time (hours), min.	4082000 h
	Ambient temperature	40 °C
	Duty cycle	100 %

### Classifications

ETIM 8.0	EC001604	ETIM 9.0	EC001604
ETIM 10.0	EC001604	ECLASS 14.0	27-24-26-08
ECLASS 15.0	27-24-26-08		

## PRO COM CAN OPEN

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Cable

Adapter cable from SUB-D to RJ45 for the PRO COM CAN OPEN communication module.



### General ordering data

Type	PRO CAB SUBD-RJ45 0.5M	Version
Order No.	<a href="#">2578530000</a>	, Sub-D socket 9 poles, RJ45 IP 20, 0,5 m
GTIN (EAN)	4050118589597	
Qty.	1 ST	
Type	PRO CAB SUBD-RJ45 1.0M	Version
Order No.	<a href="#">2578550000</a>	, Sub-D socket 9 poles, RJ45 IP 20, 1 m
GTIN (EAN)	4050118589702	
Qty.	1 ST	
Type	PRO CAB SUBD-RJ45 2.5M	Version
Order No.	<a href="#">2578560000</a>	, Sub-D socket 9 poles, RJ45 IP 20, 2,5 m
GTIN (EAN)	4050118589573	
Qty.	1 ST	