


MCP PLUS 2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The MCP Plus 2 is a flexible A3 plotter with marking options for various applications. Three easy-to-install mounting plates cover more than 250 types of Multi-Cards and label sheets.

General ordering data

Version	Marking systems, Labelling device, Plotter printing with india ink, Multicard, Labels
Order No.	2438510000
Type	MCP PLUS 2
GTIN (EAN)	4050118465389
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2022-11-04T00:00:00+01:00

MCP PLUS 2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	155 mm	Depth (inches)	6.1024 inch
Height	690 mm	Height (inches)	27.1653 inch
Width	480 mm	Width (inches)	18.8976 inch
Net weight	8300 g		

Temperatures

Ambient temperature 10 °C...35 °C

Environmental Product Compliance

RoHS Compliance Status Compliant
 REACH SVHC Lead 7439-92-1

Labelling systems

Marker type	Multicard, Labels	Feeding	Manuall mounting
Printing method	Plotter printing with india ink	Interface	USB
Software	M-Print® PRO	Type	MCP Plus 2
Supply voltage	100...240 V AC	Operating system	Windows 7, Windows 8, Windows 8.1, Windows 10
Printer driver	Windows 7, Windows 8, Windows 8.1, Windows 10	Printing speed	max. 40 cm/s
Operation with rechargeable batteries	No	Included in delivery	MCP Plus 2, MultiCard mounting plate, Printer driver, Manuals (CD), Software M-Print® PRO, Plotter pen 0.25 P-INK, Mains cable, Power supply (100-240 V AC / 5060 Hz), USB cable, Euro plug, US plug

Classifications

ETIM 8.0	EC000610	ETIM 9.0	EC000610
ETIM 10.0	EC000610	ECLASS 14.0	24-32-11-90
ECLASS 15.0	24-32-11-90		


MCP PLUS 2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Holders



Our MCP plotters complement the Weidmüller MultiCard concept and can be used with Weidmüller's M-Print® PRO software. They are particularly suitable for printing individual markers or parts of MultiCards. The positioning frame for SlimFix markers sizes 4 to 6 can be used to print MultiCards for terminals, cables, wires, and devices. The MCP label positioning frame is used to print labels.

General ordering data

Type	MCP AP PLUS	Version
Order No.	1924360000	Holder
GTIN (EAN)	4032248563548	
Qty.	1 ST	
Type	MCP AP LABELS	Version
Order No.	1924370000	Holder
GTIN (EAN)	4032248563555	
Qty.	1 ST	
Type	MCP AP SF4-6	Version
Order No.	1924310000	Holder
GTIN (EAN)	4032248563494	
Qty.	1 ST	

Inlay



Our MCP plotters complement the Weidmüller MultiCard concept and can be used with Weidmüller's M-Print® PRO software. They are particularly suitable for printing individual markers or parts of MultiCards. The positioning frame for SlimFix markers sizes 4 to 6 can be used to print MultiCards for terminals, cables, wires, and devices. The MCP label positioning frame is used to print labels.

General ordering data

Type	MCP EP	Version
Order No.	1935130000	Inlay for MC plotter
GTIN (EAN)	4032248593583	
Qty.	1 ST	

MCP PLUS 2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Cleaner



Our MCP plotters complement the Weidmüller MultiCard concept and can be used with Weidmüller's M-Print® PRO software. They are particularly suitable for printing individual markers or parts of MultiCards. The positioning frame for SlimFix markers sizes 4 to 6 can be used to print MultiCards for terminals, cables, wires, and devices. The MCP label positioning frame is used to print labels.

General ordering data

Type	P-CLEANER	Version	
Order No.	1924330000	Plotter cleaner	
GTIN (EAN)	4032248563517		
Qty.	1 ST		
Type	CLEANER 2000 25ML	Version	
Order No.	1772130000	Cleaner	
GTIN (EAN)	4032248129294		
Qty.	1 ST		

Other



Our MCP plotters complement the Weidmüller MultiCard concept and can be used with Weidmüller's M-Print® PRO software. They are particularly suitable for printing individual markers or parts of MultiCards. The positioning frame for SlimFix markers sizes 4 to 6 can be used to print MultiCards for terminals, cables, wires, and devices. The MCP label positioning frame is used to print labels.

General ordering data

Type	ADAPTER ALU STI-S	Version	
Order No.	1762440000	Identification systems, Adapter	
GTIN (EAN)	4032248044504		
Qty.	1 ST		

Felt-tip pens



Our MCP plotters complement the Weidmüller MultiCard concept and can be used with Weidmüller's M-Print® PRO software. They are particularly suitable for printing individual markers or parts of MultiCards. The positioning frame for SlimFix markers sizes 4 to 6 can be used to print MultiCards for terminals, cables, wires, and devices. The MCP label positioning frame is used to print labels.

MCP PLUS 2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

General ordering data

Type	STI WATERPROOF SCHWARZ	Version
Order No.	0508401694	Fibre pen
GTIN (EAN)	4008190017026	
Qty.	10 ST	

Plotter pens



Our MCP plotters complement the Weidmüller MultiCard concept and can be used with Weidmüller's M-Print® PRO software. They are particularly suitable for printing individual markers or parts of MultiCards. The positioning frame for SlimFix markers sizes 4 to 6 can be used to print MultiCards for terminals, cables, wires, and devices. The MCP label positioning frame is used to print labels.

General ordering data

Type	PLOTTER PEN 0.25 P-INK	Version
Order No.	1920640000	Plotter pen
GTIN (EAN)	4032248561261	
Qty.	1 ST	
Type	PLOTTER PEN 0.35 P-INK	Version
Order No.	1920650000	Plotter pen
GTIN (EAN)	4032248561278	
Qty.	1 ST	
Type	PLOTTER PEN 0.50 P-INK	Version
Order No.	1005710000	Plotter pen
GTIN (EAN)	4032248705870	
Qty.	1 ST	
Type	PLOTTER PEN 0.70 P-INK	Version
Order No.	1011450000	Plotter pen
GTIN (EAN)	4032248717897	
Qty.	1 ST	
Type	PLOTTERPEN 0,7	Version
Order No.	1011440000	Plotter pen
GTIN (EAN)	4032248717873	
Qty.	1 ST	
Type	PLOTTERPEN 0,18	Version
Order No.	1768570000	Plotter pen
GTIN (EAN)	4032248110926	
Qty.	1 ST	
Type	PLOTTERPEN 0,25	Version
Order No.	1768540000	Plotter pen
GTIN (EAN)	4032248110797	
Qty.	1 ST	
Type	PLOTTERPEN 0,35	Version
Order No.	1768550000	Plotter pen
GTIN (EAN)	4032248110803	
Qty.	1 ST	

MCP PLUS 2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	PLOTTERPEN 0,5	Version	
Order No.	1768560000	Plotter pen	
GTIN (EAN)	4032248110919		
Qty.	1 ST		

Ink



Our MCP plotters complement the Weidmüller MultiCard concept and can be used with Weidmüller's M-Print® PRO software. They are particularly suitable for printing individual markers or parts of MultiCards. The positioning frame for SlimFix markers sizes 4 to 6 can be used to print MultiCards for terminals, cables, wires, and devices. The MCP label positioning frame is used to print labels.

General ordering data

Type	P-INK 2.0	Version	
Order No.	1924340000	Ink	
GTIN (EAN)	4032248563524		
Qty.	1 ST		
Type	INK 2000 25ML	Version	
Order No.	1772120000	Ink	
GTIN (EAN)	4032248129287		
Qty.	1 ST		

Other



Our MCP plotters complement the Weidmüller MultiCard concept and can be used with Weidmüller's M-Print® PRO software. They are particularly suitable for printing individual markers or parts of MultiCards. The positioning frame for SlimFix markers sizes 4 to 6 can be used to print MultiCards for terminals, cables, wires, and devices. The MCP label positioning frame is used to print labels.

General ordering data

Type	MCP PLUS 2 COVER	Version	
Order No.	2493070000		
GTIN (EAN)	4050118502930		
Qty.	1 ST		