

PRO COM DISPLAY 7S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Weidmüller's plug-in communication modules enable individual components to exchange relevant data with the cloud. This lays the foundation for targeted process optimization using condition monitoring and remote controllability - factors that play a decisive role in increasing efficiency, quality, process stability and availability can contribute. The communication modules are designed according to IP20 protected, can be operated without tools and can be flexibly adapted to different customizable communication protocols.

General ordering data

Version	Communication module
Order No.	2466960000
Type	PRO COM DISPLAY 7S
GTIN (EAN)	4050118481808
Qty.	1 items

PRO COM DISPLAY 7S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E258476
Certificate no. (cULusEX)	E470829

Dimensions and weights

Depth	33.6 mm	Depth (inches)	1.3228 inch
Height	74.4 mm	Height (inches)	2.9291 inch
Width	34 mm	Width (inches)	1.3386 inch
Net weight	36 g		

Temperatures

Storage temperature	Operating temperature	-25 °C...70 °C
---------------------	-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cI
REACH SVHC	Lead 7439-92-1, Lead monoxide 1317-36-8
SCIP	d62541f7-8058-4336-b693-7303c8b40800

General data

Protection degree	IP20	
MTTF	According to Standard	SN 29500
	Operating time (hours), min.	2505000 h
	Ambient temperature	40 °C
	Duty cycle	100 %

Electrical safety (applied standards)

Protection against dangerous shock currents	Acc. to VDE0106-101	Safety transformers for switch-mode power supplies	According to EN 61558-2-16
---	---------------------	--	----------------------------

Classifications

ETIM 8.0	EC001604	ETIM 9.0	EC001604
ETIM 10.0	EC001604	ECLASS 14.0	27-24-26-08
ECLASS 15.0	27-24-26-08		

PRO COM DISPLAY 7S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

