

ES EPG/HPG 60 WM 35

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

| | |
|------------|--|
| Version | Crimping tool insert, 35mm ² , WM crimp |
| Order No. | 2469570000 |
| Type | ES EPG/HPG 60 WM 35 |
| GTIN (EAN) | 4050118483826 |
| Qty. | 1 items |

ES EPG/HPG 60 WM 35

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 22 mm | Depth (inches) | 0.8661 inch |
| Height | 42 mm | Height (inches) | 1.6535 inch |
| Width | 42 mm | Width (inches) | 1.6535 inch |
| Net weight | 124.96 g | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Crimp inserts

| | | | |
|----------------------|------|----------------------------|----|
| Crimping width | 5 mm | Crimp cross-section copper | 35 |
| Crimping width in mm | 5 | | |

Description of contact

| | | | |
|-----------------------------------|-----------------------|-----------------------------------|--------------------|
| Type of contact | Euro series cable lug | Conductor cross-section, max. AWG | 2 |
| Conductor cross-section, min. AWG | 2 | Crimping range, max. | 35 mm ² |

tool data crimping

| | |
|-------------------------|----------------------------|
| Crimping type/profile | WM crimp |
| Cable lug cross section | nominal 35 mm ² |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001282 | ETIM 9.0 | EC001282 |
| ETIM 10.0 | EC001282 | ECLASS 14.0 | 21-04-90-90 |
| ECLASS 15.0 | 21-04-90-90 | | |

ES EPG/HPG 60 WM 35

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Tools




Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

| | | |
|------------|----------------------------|---|
| Type | EPG 60 | Version |
| Order No. | 2453810000 | Pressing tools, Tools, Pressing tool, 6mm ² , 300mm ² , Hexagonal crimp, WM crimp, Indent crimp, Trapezoidal crimp, Oval crimping |
| GTIN (EAN) | 4050118468434 | |
| Qty. | 1 ST | |
| Type | HPG 60 | Version |
| Order No. | 2453820000 | 6mm ² , 300mm ² , Hexagonal crimp, WM crimp, Indent crimp, Trapezoidal crimp, Oval crimping |
| GTIN (EAN) | 4050118468427 | |
| Qty. | 1 ST | |

35 mm²



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

| | | |
|------------|----------------------------|---|
| Type | KRN-M6/-35 | Version |
| Order No. | 1496540000 | cable lug, terminal end,35 mm ² ,35 mm ² - 35 mm ² |
| GTIN (EAN) | 4050118306156 | |
| Qty. | 100 ST | |
| Type | KRN-M8/-35 | Version |
| Order No. | 1496550000 | cable lug, terminal end,35 mm ² ,35 mm ² - 35 mm ² |
| GTIN (EAN) | 4050118305913 | |
| Qty. | 100 ST | |
| Type | KRN-M10/-35 | Version |
| Order No. | 1496570000 | cable lug, terminal end,35 mm ² ,35 mm ² - 35 mm ² |
| GTIN (EAN) | 4050118305920 | |
| Qty. | 100 ST | |

ES EPG/HPG 60 WM 35

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|---|
| Type | KRN-M12/-35 | Version |
| Order No. | 1496580000 | cable lug, terminal end,35 mm ² ,35 mm ² - 35 mm ² |
| GTIN (EAN) | 4050118306019 | |
| Qty. | 100 ST | |
| Type | KRN-M6/-35 S | Version |
| Order No. | 1494790000 | cable lug, terminal end,35 mm ² ,35 mm ² - 35 mm ² |
| GTIN (EAN) | 4050118304466 | |
| Qty. | 25 ST | |
| Type | KRN-M8/-35 S | Version |
| Order No. | 1494810000 | cable lug, terminal end,35 mm ² ,35 mm ² - 35 mm ² |
| GTIN (EAN) | 4050118304374 | |
| Qty. | 25 ST | |
| Type | KWN-M6/-35 90 | Version |
| Order No. | 1495910000 | cable lug, terminal end,35 mm ² ,35 mm ² - 35 mm ² |
| GTIN (EAN) | 4050118305418 | |
| Qty. | 100 ST | |
| Type | KWN-M8/-35 90 | Version |
| Order No. | 1495920000 | cable lug, terminal end,35 mm ² ,35 mm ² - 35 mm ² |
| GTIN (EAN) | 4050118305548 | |
| Qty. | 100 ST | |
| Type | KWN-M10/-35 90 | Version |
| Order No. | 1495930000 | cable lug, terminal end,35 mm ² ,35 mm ² - 35 mm ² |
| GTIN (EAN) | 4050118305173 | |
| Qty. | 100 ST | |
| Type | KWN-M12/-35 90 | Version |
| Order No. | 1495940000 | cable lug, terminal end,35 mm ² ,35 mm ² - 35 mm ² |
| GTIN (EAN) | 4050118305623 | |
| Qty. | 100 ST | |
| Type | KWN-M14/-35 90 | Version |
| Order No. | 1494640000 | cable lug, terminal end,35 mm ² ,35 mm ² - 35 mm ² |
| GTIN (EAN) | 4050118304350 | |
| Qty. | 100 ST | |
| Type | KWN-M16/-35 90 | Version |
| Order No. | 1494690000 | cable lug, terminal end,35 mm ² ,35 mm ² - 35 mm ² |
| GTIN (EAN) | 4050118304268 | |
| Qty. | 100 ST | |
| Type | KWN-M6/-35 45 | Version |
| Order No. | 1496220000 | cable lug, terminal end,35 mm ² ,35 mm ² - 35 mm ² |
| GTIN (EAN) | 4050118305852 | |
| Qty. | 50 ST | |
| Type | KWN-M8/-35 45 | Version |
| Order No. | 1496230000 | cable lug, terminal end,35 mm ² ,35 mm ² - 35 mm ² |
| GTIN (EAN) | 4050118305968 | |
| Qty. | 50 ST | |
| Type | KWN-M10/-35 45 | Version |
| Order No. | 1496240000 | cable lug, terminal end,35 mm ² ,35 mm ² - 35 mm ² |
| GTIN (EAN) | 4050118306217 | |
| Qty. | 50 ST | |
| Type | KWN-M12/-35 45 | Version |
| Order No. | 1496250000 | cable lug, terminal end,35 mm ² ,35 mm ² - 35 mm ² |
| GTIN (EAN) | 4050118306002 | |
| Qty. | 50 ST | |

ES EPG/HPG 60 WM 35

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|--|
| Type | VSTN/-35 | Version |
| Order No. | 1494740000 | cable lug, terminal end,35 mm ² ,35 mm ² ,None |
| GTIN (EAN) | 4050118304428 | |
| Qty. | 50 ST | |
| Type | KP-M6/-35 | Version |
| Order No. | 1498020000 | cable lug, terminal end,35 mm ² |
| GTIN (EAN) | 4050118307313 | |
| Qty. | 100 ST | |
| Type | KP-M8/-35 | Version |
| Order No. | 1498030000 | cable lug, terminal end,35 mm ² |
| GTIN (EAN) | 4050118307511 | |
| Qty. | 100 ST | |
| Type | KP-M10/-35 | Version |
| Order No. | 1498040000 | cable lug, terminal end,35 mm ² |
| GTIN (EAN) | 4050118307337 | |
| Qty. | 100 ST | |
| Type | KP-M12/35 | Version |
| Order No. | 1498050000 | cable lug, terminal end,35 mm ² |
| GTIN (EAN) | 4050118307320 | |
| Qty. | 100 ST | |
| Type | KP-M16/-35 | Version |
| Order No. | 1498060000 | cable lug, terminal end,35 mm ² |
| GTIN (EAN) | 4050118307382 | |
| Qty. | 100 ST | |
| Type | KWPN-M6/-35 90 | Version |
| Order No. | 1497540000 | cable lug, terminal end,35 mm ² |
| GTIN (EAN) | 4050118306996 | |
| Qty. | 100 ST | |
| Type | KWPN-M8/-35 90 | Version |
| Order No. | 1497550000 | cable lug, terminal end,35 mm ² |
| GTIN (EAN) | 4050118307146 | |
| Qty. | 100 ST | |
| Type | KWPN-M10/-35 90 | Version |
| Order No. | 1497570000 | cable lug, terminal end,35 mm ² |
| GTIN (EAN) | 4050118307153 | |
| Qty. | 100 ST | |
| Type | KWPN-M12/-35 90 | Version |
| Order No. | 1497580000 | cable lug, terminal end,35 mm ² |
| GTIN (EAN) | 4050118306682 | |
| Qty. | 100 ST | |
| Type | VPN/-35 | Version |
| Order No. | 1498650000 | cable lug, terminal end,35 mm ² ,35 mm ² ,None |
| GTIN (EAN) | 4050118308143 | |
| Qty. | 100 ST | |
| Type | KQN-M6/-35 | Version |
| Order No. | 1494170000 | cable lug, terminal end,35 mm ² |
| GTIN (EAN) | 4050118304015 | |
| Qty. | 50 ST | |
| Type | KQN-M8/-35 | Version |
| Order No. | 1494180000 | cable lug, terminal end,35 mm ² |
| GTIN (EAN) | 4050118304022 | |
| Qty. | 50 ST | |

ES EPG/HPG 60 WM 35

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|--|
| Type | KQN-M10/-35 | Version |
| Order No. | 1494190000 | cable lug, terminal end,35 mm ² |
| GTIN (EAN) | 4050118303780 | |
| Qty. | 50 ST | |
| Type | KQN-M12/-35 | Version |
| Order No. | 1493130000 | cable lug, terminal end,35 mm ² |
| GTIN (EAN) | 4050118302837 | |
| Qty. | 50 ST | |
| Type | KQN-M16/-35 | Version |
| Order No. | 1493140000 | cable lug, terminal end,35 mm ² |
| GTIN (EAN) | 4050118302851 | |
| Qty. | 50 ST | |
| Type | KQN-M20/-35 | Version |
| Order No. | 1493520000 | cable lug, terminal end,35 mm ² |
| GTIN (EAN) | 4050118303124 | |
| Qty. | 50 ST | |
| Type | KSN/-35 | Version |
| Order No. | 1492810000 | cable lug, terminal end,35 mm ² ,35 mm ² |
| GTIN (EAN) | 4050118302639 | |
| Qty. | 50 ST | |
| Type | VPLN/-35 | Version |
| Order No. | 1492920000 | cable lug, terminal end,35 mm ² ,35 mm ² ,None |
| GTIN (EAN) | 4050118302752 | |
| Qty. | 100 ST | |
| Type | VSTN/35 | Version |
| Order No. | 1493060000 | cable lug, terminal end,35 mm ² ,35 mm ² ,None |
| GTIN (EAN) | 4050118302943 | |
| Qty. | 100 ST | |