

## CUTFIX 8 INTERFACE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



- For automatically cutting individual wires to length
- High repeat accuracy due to the precise servo DC drive
- Interface for controlling the automatic cutter via an IBM-compatible PC

### General ordering data

Version	Cutting machine
Order No.	<a href="#">2580010000</a>
Type	CUTFIX 8 INTERFACE
GTIN (EAN)	4050118605839
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2025-01-06T00:00:00+01:00
Alternative product	<a href="#">CUTFIX PRO</a>

**CUTFIX 8 INTERFACE**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Depth	360 mm	Depth (inches)	14.1732 inch
Height	470 mm	Height (inches)	18.5039 inch
Width	380 mm	Width (inches)	14.9606 inch
Net weight	20809 g		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	d2df479e-2b79-4e98-adc7-b03577df98ae

**Automatic cutting**

Correction for length	Slip correction in mm can be programmed to suit the part.	Amount pre-selection, max.	Adjustable part quantity code
Drive	electrical	Storage	Up to 2,000 cutting jobs
Keyboard	Touch display	Feeding speed, max.	1.5 m/s
Indicator display	LCD display	Length pre-selection, max.	999999 mm
Length pre-selection, min.	2 mm	Interface	USB 1.1, USB 2.0
Software	for data exchanging with IBM-compatible PC, Integrated interface to read CAE data	Aperture (max. diameter)	8 mm outer diameter
Electrical connection	100 - 240 V / 50 Hz / 240 VA	Flexible/solid individual conductors	max. 10 mm <sup>2</sup> / max. 2.5 mm <sup>2</sup>

**Classifications**

ETIM 8.0	EC002778	ETIM 9.0	EC002778
ETIM 10.0	EC002778	ECLASS 14.0	17-13-01-01
ECLASS 15.0	17-13-01-01		


## CUTFIX 8 INTERFACE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

## Accessories

[www.weidmueller.com](http://www.weidmueller.com)

### Accessories / replacement parts



- For automatically cutting individual wires to length
- High repeat accuracy due to the precise servo DC drive
- Interface for controlling the automatic cutter via an IBM-compatible PC

### General ordering data

Type	AIMESA V CUTFIX	Version	
Order No.	<a href="#">9054740000</a>	Accessories, Replacement part	
GTIN (EAN)	4032248 1045 12		
Qty.	1 ST		