

IE-FC-IP-PWB**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

General ordering data

Version	FrontCom, Insert plate, unshielded
Order No.	2548060000
Type	IE-FC-IP-PWB
GTIN (EAN)	4050118557596
Qty.	1 items

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E223801

Dimensions and weights

Height	19.5 mm	Height (inches)	0.7677 inch
Width	51.5 mm	Width (inches)	2.0276 inch
Length	90.5 mm	Length (inches)	3.563 inch
Net weight	14.82 g		

Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	8a473a8a-33d4-43 18-8088-c28f0 19e7f77

General data

Product type	Insert plate, unshielded	Material	Polycarbonate PC
--------------	--------------------------	----------	------------------

Inserts

Insert Power large	1
--------------------	---

General standards

Certificate No. (cURus)	E223801	Certificate No. (CSA)	2000039-80039714
-------------------------	---------	-----------------------	------------------

Classifications

ETIM 8.0	EC000456	ETIM 9.0	EC000456
ETIM 10.0	EC000456	ECLASS 14.0	27-18-28-92
ECLASS 15.0	27-18-28-92		


IE-FC-IP-PWB

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	ESG 7/20 SIRIUS MC NE WS	Version	
Order No.	1736181044	ESG, Device markers x 20 mm, PA 66, Colour: white, pluggable	
GTIN (EAN)	4008190985950		
Qty.	200 ST		

Power sockets



FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

General ordering data

Type	IE-FCI-PWB-AU	Version	
Order No.	1450830000	FrontCom, Insert Power large, Type I, Socket connector, AU, 15 A	
GTIN (EAN)	4050118255591		
Qty.	1 ST		
Type	IE-FCI-PWB-AU-10A	Version	
Order No.	1546590000	FrontCom, Insert Power large, Type I, Socket connector, AU, 10 A	
GTIN (EAN)	4050118351842		
Qty.	1 ST		
Type	IE-FCI-PWB-CH	Version	
Order No.	1450780000	FrontCom, Insert Power large, Type J, Socket connector, CH	
GTIN (EAN)	4050118255553		
Qty.	1 ST		
Type	IE-FCI-PWB-CN	Version	
Order No.	1450790000	FrontCom, Insert Power large, Type I, Socket connector, CN	
GTIN (EAN)	4050118255386		
Qty.	1 ST		

IE-FC-IP-PWB

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	IE-FCI-PWB-FR/B/CZ	Version
Order No.	2426700000	FrontCom, Insert Power large, Type E, Socket connector, FR, CZ
GTIN (EAN)	4050118435139	
Qty.	1 ST	
Type	IE-FCI-PWB-DE	Version
Order No.	1450730000	FrontCom, Insert Power large, Type F, Socket connector, DE
GTIN (EAN)	4050118255546	
Qty.	1 ST	
Type	IE-FCI-PWB-FR	Version
Order No.	1450750000	FrontCom, Insert Power large, Type E, Socket connector, FR
GTIN (EAN)	4050118255706	
Qty.	1 ST	
Type	IE-FCI-PWB-FR-OR	Version
Order No.	2007230000	FrontCom, Insert Power large, Type E, Socket connector, FR, orange
GTIN (EAN)	4050118392135	
Qty.	1 ST	
Type	IE-FCI-PWB-GB	Version
Order No.	1450770000	FrontCom, Insert Power large, Type G, Socket connector, GB
GTIN (EAN)	4050118255577	
Qty.	1 ST	
Type	IE-FCI-PWB-IND	Version
Order No.	2500710000	FrontCom, Insert Power large, Type D, Socket connector, IN
GTIN (EAN)	4050118526745	
Qty.	1 ST	
Type	IE-FCI-PWB-ISR	Version
Order No.	2531060000	FrontCom, Insert Power large, Type H, Socket connector, ISR
GTIN (EAN)	4050118541175	
Qty.	1 ST	
Type	IE-FCI-PWS-IT	Version
Order No.	1450810000	FrontCom, Insert Power small, Type L, Socket connector, IT, EU
GTIN (EAN)	4050118255720	
Qty.	1 ST	

Slotted screwdriver



Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. ChromTop tip, SoftFinish grip

General ordering data

Type	SDS 0.4X2.5X75	Version
Order No.	9009030000	Screwdriver, Screwdriver
GTIN (EAN)	4032248266944	
Qty.	1 ST	

Accessories

Accessories for FrontCom Vario



General ordering data

Type	IE-FC-PWPC	Version	
Order No.	1450820000	FrontCom, Touch-safe protection, Single frame	
GTIN (EAN)	4050118255584		
Qty.	1 ST		