

PRO CASE UL**Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26
D-32758 Detmold
Germanywww.weidmueller.com

Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

General ordering data

Version	Tool case with contents
Order No.	2602260000
Type	PRO CASE UL
GTIN (EAN)	4050118613025
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2026-02-28T00:00:00+01:00

PRO CASE UL

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	170 mm
Height	400 mm
Width	480 mm
Net weight	6563 g

Depth (inches)	6.6929 inch
Height (inches)	15.748 inch
Width (inches)	18.8976 inch

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

Technical data

Description of article	Tool case
------------------------	-----------

Classifications

ETIM 8.0	EC000149
ETIM 10.0	EC000149
ECLASS 15.0	21-04-50-03

ETIM 9.0	EC000149
ECLASS 14.0	21-04-50-03

PRO CASE UL

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



PRO CASE UL

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Empty



Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

General ordering data

Type	PRO CASE LEER	Version
Order No.	9202470000	Assortment box
GTIN (EAN)	4032248495788	
Qty.	1 ST	

Cutting tools



Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

General ordering data

Type	KT 8	Version
Order No.	9002650000	Cutting tools, Cutting tool for one-hand operation
GTIN (EAN)	4008190020163	
Qty.	1 ST	

VDE-insulated combination pliers



When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

PRO CASE UL

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

General ordering data

Type	KBZ 180	Version
Order No.	9046290000	Pliers
GTIN (EAN)	4032248356485	
Qty.	1 ST	

VDE-insulated diagonal-cutting pliers



When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

General ordering data

Type	SE HD 180	Version
Order No.	9046330000	Diagonal-cutting pliers
GTIN (EAN)	4032248357635	
Qty.	1 ST	

VDE insulated telephone pliers



When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

General ordering data

Type	FRZ S 160	Version
Order No.	9046370000	Pliers
GTIN (EAN)	4032248357673	
Qty.	1 ST	

PRO CASE UL

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Tools



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

Type	STRIPAX	Version
Order No.	9005000000	Tools, Stripping and cutting tool
GTIN (EAN)	4008190072506	
Qty.	1 ST	
Type	STRIPPER ROUND TOP	Version
Order No.	9918050000	Sheathing strippers
GTIN (EAN)	4032248359165	
Qty.	1 ST	
Type	STRIPAX ULTIMATE	Version
Order No.	1468880000	Tools, Stripping and cutting tool
GTIN (EAN)	4050118274158	
Qty.	1 ST	
Type	AM 16	Version
Order No.	9204190000	Tools, Sheathing strippers
GTIN (EAN)	4032248608133	
Qty.	1 ST	

Crimping tools



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Type	PZ 10 HEX	Version
Order No.	1445070000	Crimping tool for wire-end ferrules, 0.25mm ² , 10mm ² , Hexagonal
GTIN (EAN)	4050118250312	crimp
Qty.	1 ST	

PRO CASE UL

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Socket wrench sets



Allen key made from fully hardened, high-alloy chromium-vanadium- steel, acc. to DIN ISO 2936 L (DIN 911), high-quality refined surface.

General ordering data

Type	SK WSD-S 1.5-10,0	Version
Order No.	9008850000	Mounting tool
GTIN (EAN)	4032248266609	
Qty.	1 ST	

Set of non-insulated screwdrivers



Weidmüller SoftFinish screwdriver for general uses, blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, matt chrome finish.

General ordering data

Type	SD SET S2.5-5.5/PH1/2	Version
Order No.	2749200000	Screwdriver set
GTIN (EAN)	4050118895506	
Qty.	1 ST	

Screwdriver Sets



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Type	SDI SET SLIM S3.5-6.5/P...	Version
Order No.	2749580000	Mounting tool
GTIN (EAN)	4050118896329	
Qty.	1 ST	

PRO CASE UL

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Cabinet keys



Crimped conductors are fixed in their respective wiring spaces by screws or a direct plug-in feature. Weidmüller can supply a wide range of tools for screwing.

General ordering data

Type CROSS-KEY UNIVERSAL

Order No. [9918130000](#)

GTIN (EAN) 4032248371112

Qty. 1 ST

Version

Universal key

with LCD Display



The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LCD-Display
- acc. to VDE standard,
- high peak voltage strength
- the right tester for every application

General ordering data

Type VT DIGI PRO

Order No. [9918870000](#)

GTIN (EAN) 4032248405756

Qty. 1 ST

Version

Testing tools, 2-pole voltage tester

Non-contact voltage tester



- Reacts from a distance of 4 mm
- No current flow necessary thanks to capacitive method
- Detects concealed broken wires with a tolerance of just a few millimetres
- Detects voltage-conducting wires in sockets, cable reels, distributors, etc.
- Display: visual or both visual and acoustic
- including a flashlight function with the VT LCL

General ordering data

Type VT LCL

Order No. [2436670000](#)

GTIN (EAN) 4050118450033

Qty. 1 ST

Version

Testing tools, Cable detector

PRO CASE UL

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Continuity testers



The fully insulated plastic housings of our continuity testers are shockproof and unbreakable, making these instruments ideal for daily use, even in tough conditions. The integrated torch makes it easier to locate defective cables quickly and safely. The results of the continuity test can be conveyed visually and acoustically.

General ordering data

Type	VT CTL	Version
Order No.	2436690000	Testing tools, Testing device
GTIN (EAN)	4050118450040	
Qty.	1 ST	

Assortment of wire end ferrules with plastic collar



Box filled with wire end ferrules with plastic collar:

- in Weidmüller colour code
- DIN colour code

General ordering data

Type	H-BOX 0,5-2,5QMM DIN	Version
Order No.	9025430000	Assortment of wire end ferrules, Box, Colour code: DIN
GTIN (EAN)	4008190337162	
Qty.	1 ST	

Measuring instruments



Precision tools from Weidmüller are in use worldwide. Weidmüller takes this responsibility seriously and offers comprehensive services.

Tools should still function perfectly even after many years of constant use. Weidmüller therefore offers its customers the "Tool Certification" service. This technical testing routine allows Weidmüller to guarantee the proper functioning and quality of its tools.

General ordering data

Type	FLEXIMET 5 M	Version
Order No.	2534210000	Measuring tape
GTIN (EAN)	4050118545975	
Qty.	1 ST	