

**PRO CASE 16****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

**General ordering data**

Version	Tool case with contents
Order No.	<a href="#">2602270000</a>
Type	PRO CASE 16
GTIN (EAN)	4050118613087
Qty.	1 items

## PRO CASE 16

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	170 mm	Depth (inches)	6.6929 inch
Height	400 mm	Height (inches)	15.748 inch
Width	480 mm	Width (inches)	18.8976 inch
Net weight	6062 g		

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

## Technical data

Description of article	Tool case
------------------------	-----------

## Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ETIM 9.0	EC000149
ETIM 10.0	EC000149	ECLASS 9.0	21-04-50-03
ECLASS 9.1	21-10-01-90	ECLASS 10.0	21-04-50-03
ECLASS 11.0	21-04-50-03	ECLASS 12.0	21-04-50-03
ECLASS 13.0	21-04-50-03	ECLASS 14.0	21-04-50-03
ECLASS 15.0	21-04-50-03		



## PRO CASE 16

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Empty



Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

## General ordering data

Type	PRO CASE LEER	Version
Order No.	<a href="#">9202470000</a>	Assortment box
GTIN (EAN)	4032248495788	
Qty.	1 ST	

## Cutting tools



Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

## General ordering data

Type	KT 8	Version
Order No.	<a href="#">9002650000</a>	Cutting tools, Cutting tool for one-hand operation
GTIN (EAN)	4008190020163	
Qty.	1 ST	

## VDE-insulated combination pliers



When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose. Weidmüller offers a complete line of pliers which comply with national and international testing standards. All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

## PRO CASE 16

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## General ordering data

Type	KBZ 180	Version	
Order No.	<a href="#">9046290000</a>	Pliers	
GTIN (EAN)	4032248356485		
Qty.	1 ST		

## VDE-insulated diagonal-cutting pliers



When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

## General ordering data

Type	SE HD 180	Version	
Order No.	<a href="#">9046330000</a>	Diagonal-cutting pliers	
GTIN (EAN)	4032248357635		
Qty.	1 ST		

## VDE insulated telephone pliers



When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

## General ordering data

Type	FRZ S 160	Version	
Order No.	<a href="#">9046370000</a>	Pliers	
GTIN (EAN)	4032248357673		
Qty.	1 ST		

## Accessories

### Tools



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

### General ordering data

Type	STRIPAX	Version
Order No.	<a href="#">9005000000</a>	Tools, Stripping and cutting tool
GTIN (EAN)	4008190072506	
Qty.	1 ST	
Type	STRIPAX 16	Version
Order No.	<a href="#">9005610000</a>	Tools, Stripping and cutting tool
GTIN (EAN)	4008190183875	
Qty.	1 ST	
Type	AM 16	Version
Order No.	<a href="#">9204190000</a>	Tools, Sheathing strippers
GTIN (EAN)	4032248608133	
Qty.	1 ST	

### Crimping tools



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

### General ordering data

Type	PZ 6 ROTO L	Version
Order No.	<a href="#">1444050000</a>	Pressing tool, Crimping tool for wire-end ferrules, 0.14mm², 6mm²,
GTIN (EAN)	4050118248593	Trapezoidal crimp
Qty.	1 ST	
Type	PZ 16	Version
Order No.	<a href="#">9012600000</a>	Pressing tool, Crimping tool for wire-end ferrules, 6mm², 16mm²,
GTIN (EAN)	4008190035440	Indent crimp
Qty.	1 ST	

## PRO CASE 16

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Screwdriver Sets



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

## General ordering data

Type	SDI SET SLIM S3.5-6.5/P...	Version
Order No.	<a href="#">2749580000</a>	Mounting tool
GTIN (EAN)	4050118896329	
Qty.	1 ST	

## with LCD Display



The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LCD-Display
- acc. to VDE standard,
- high peak voltage strength
- the right tester for every application

## General ordering data

Type	VT DIGI PRO	Version
Order No.	<a href="#">9918870000</a>	Testing tools, 2-pole voltage tester
GTIN (EAN)	4032248405756	
Qty.	1 ST	

## Non-contact voltage tester



- Reacts from a distance of 4 mm
- No current flow necessary thanks to capacitive method
- Detects concealed broken wires with a tolerance of just a few millimetres
- Detects voltage-conducting wires in sockets, cable reels, distributors, etc.
- Display: visual or both visual and acoustic
- including a flashlight function with the VT LCL

## General ordering data

Type	VT LCL	Version
Order No.	<a href="#">2436670000</a>	Testing tools, Cable detector
GTIN (EAN)	4050118450033	
Qty.	1 ST	

## PRO CASE 16

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Continuity testers



The fully insulated plastic housings of our continuity testers are shockproof and unbreakable, making these instruments ideal for daily use, even in tough conditions. The integrated torch makes it easier to locate defective cables quickly and safely. The results of the continuity test can be conveyed visually and acoustically.

## General ordering data

Type	VT CTL	Version	
Order No.	<a href="#">2436690000</a>	Testing tools, Testing device	
GTIN (EAN)	4050118450040		
Qty.	1 ST		

## Assortment of wire end ferrules with plastic collar



Box filled with wire end ferrules with plastic collar:

- in Weidmüller colour code
- DIN colour code

## General ordering data

Type	H-BOX 0,5-2,5QMM DIN	Version	
Order No.	<a href="#">9025430000</a>	Assortment of wire end ferrules, Box, Colour code: DIN	
GTIN (EAN)	4008190337162		
Qty.	1 ST		
Type	H-BOX 4,0-16,0QMM DIN	Version	
Order No.	<a href="#">9025400000</a>	Assortment of wire end ferrules, Box, Colour code: DIN	
GTIN (EAN)	4008190341596		
Qty.	1 ST		

## Measuring instruments



Precision tools from Weidmüller are in use worldwide. Weidmüller takes this responsibility seriously and offers comprehensive services.

Tools should still function perfectly even after many years of constant use. Weidmüller therefore offers its customers the "Tool Certification" service. This technical testing routine allows Weidmüller to guarantee the proper functioning and quality of its tools.



## Accessories

### General ordering data

Type	FLEXIMET 5 M	Version	
Order No.	<a href="#">2534210000</a>	Measuring tape	
GTIN (EAN)	4050118545975		
Qty.	1 ST		