

HDC MBUS8 F AWG20

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Comprehensive portfolio for flexible on site data cabling: from dedicated tools to Cat.#5 D coded and Cat.#6 X coded connectors, as well as robust shielding sleeves. These components enable reliable, field assembled data connections – ideal for industrial applications, quick installation, and maximum flexibility.

General ordering data

Version	Crimp contact
Order No.	2565990000
Type	HDC MBUS8 F AWG20
GTIN (EAN)	4050118575842
Qty.	100 items

HDC MBUS8 F AWG20

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Net weight 0 g

Temperatures

Limit temperature -40 °C ... 90 °C

Environmental Product Compliance

RoHS Compliance Status Compliant with exemption
RoHS Exemption (if applicable/known) 6c
REACH SVHC Lead 7439-92-1
SCIP 6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

General data

Contact diameter, male Ø	0.6 mm	Stripping length, rated connection	4 mm
Type of connection	Crimp connection	Version insert	MBUS
Conductor cross-section, max.	0.5 mm ²	Conductor cross-section, min.	0.5 mm ²
Surface finish	gold	Plugging cycles	≤ 100
Type	Female	Basic material	Copper alloy
Series	ModuPlug	Production methods	turned
Material of contact	Copper alloy		

General data

Contact surface	Gold-plated	Transmission rate	10 Gbps
Nominal current	0.5 A	Plugging cycles	≤ 100
Type	Female		

Classifications


ETIM 8.0	EC000796	ETIM 9.0	EC000796
ETIM 10.0	EC000796	ECLASS 14.0	27-44-02-04
ECLASS 15.0	27-44-02-04		

HDC MBUS8 F AWG20

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



HDC MBUS8 F AWG20

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

Tools



Comprehensive portfolio for flexible on site data cabling: from dedicated tools to Cat.#5 D coded and Cat.#6 X coded connectors, as well as robust shielding sleeves. These components enable reliable, field assembled data connections – ideal for industrial applications, quick installation, and maximum flexibility.

General ordering data

Type	HDC MBUS CL X/D 0.6/1.0	Version
Order No.	2592680000	Locator for crimping tool
GTIN (EAN)	4050118603781	
Qty.	1 ST	
Type	HDC MBUS CT X/D 0.6/1.0	Version
Order No.	2592650000	Crimping tool for contacts
GTIN (EAN)	4050118603774	
Qty.	1 ST	