

HDC HP550 ABGH CR 1P

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The protective housing is manufactured from seawater-resistant aluminium using pressure die casting. High standards of water and dust protection, as well as particularly high impact resistance, are the hallmarks of this housing series. A sophisticated two-stage surface coating ensures years of reliability. All screws, crimp contacts and other exterior accessory parts are made of corrosion-resistant stainless steel.

General ordering data

Order No.	2568530000
Type	HDC HP550 ABGH CR 1P
GTIN (EAN)	4050118776638
Qty.	1 items

HDC HP550 ABGH CR 1P

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data**Approvals**

Approvals



ROHS Conform

Dimensions and weights

Net weight 255 g

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Design of housing	Bulkhead housing	UL 94 flammability rating	None
Colour	black	Surface finish	Powder-coated
Free from halogens	false	Protection degree	IP68, in plugged condition

General data

Colour	black	Surface finish	Powder-coated
--------	-------	----------------	---------------

Important note

Product information	Depending on the intended operation, internally generated voltages can superimpose the working voltage and contain corresponding peaks. It is imperative to ensure that these peak voltages do not exceed the rated voltage. For applications outside of this specification, please contact us.
---------------------	---

Classifications

ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		

HDC HP550 ABGH CR 1P

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Crimp contacts



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

Type	HDC HP 550 F 25	Version
Order No.	1220570000	HDC insert, Female, Crimp connection, Installation size: 550
GTIN (EAN)	4050118003840	
Qty.	1 ST	
Type	HDC HP 550 F 50	Version
Order No.	1177100000	HDC insert, Female, Crimp connection, Installation size: 550
GTIN (EAN)	4032248970919	
Qty.	1 ST	
Type	HDC HP 550 F 70	Version
Order No.	1268820000	HDC insert, Female, Crimp connection, Installation size: 550
GTIN (EAN)	4050118057584	
Qty.	1 ST	
Type	HDC HP 550 F 95	Version
Order No.	1079810000	HDC insert, Female, Crimp connection, Installation size: 550
GTIN (EAN)	4032248841707	
Qty.	1 ST	
Type	HDC HP 550 F 150	Version
Order No.	1079830000	HDC insert, Female, Crimp connection, Installation size: 550
GTIN (EAN)	4032248842018	
Qty.	1 ST	
Type	HDC HP 550 F 120	Version
Order No.	1079820000	HDC insert, Female, Crimp connection, Installation size: 550
GTIN (EAN)	4032248841806	
Qty.	1 ST	
Type	HDC HP 550 F 185	Version
Order No.	1079840000	HDC insert, Female, Crimp connection, Installation size: 550
GTIN (EAN)	4032248841905	
Qty.	1 ST	
Type	HDC HP 550 F 240	Version
Order No.	1120600000	HDC insert, Female, Crimp connection, Installation size: 550
GTIN (EAN)	4032248901609	
Qty.	1 ST	