

## CRIMPFIX R VARIO

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

### General ordering data

Version	Automatic stripper and crimper
Order No.	<a href="#">2580000000</a>
Type	CRIMPFIX R VARIO
GTIN (EAN)	4050118605846
Qty.	1 items

## CRIMPFIX R VARIO

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Depth	485 mm	Depth (inches)	19.0944 inch
Height	565 mm	Height (inches)	22.2441 inch
Width	335 mm	Width (inches)	13.189 inch
Net weight	25265 g		

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	d2df479e-2b79-4e98-adc7-b03577df98ae

### PW65 maintenance - automatic stripping/crimping

Stripping range	0.5 - 2.5 mm <sup>2</sup> (~AWG 20-14)	Drive	Electropneumatic
Pulse time	approx. 2 s	Crimping	Trapezoidal
Wire end ferrules cross-section, max.	2.5 mm <sup>2</sup>	Wire end ferrules cross-section, min.	0.5 mm <sup>2</sup>
Crimping length	8/10 mm	Consumables	Linked wire-end ferrules
Length of wire-end ferrule	14/16 mm	Compressed-air connection	5 - 5.5 bar
Insertion length, min.	27 mm	Electrical connection	100 - 240 V / 50/60 Hz / 16 VA

### Classifications

ETIM 8.0	EC002778	ETIM 9.0	EC002778
ETIM 10.0	EC002778	ECLASS 14.0	17-13-01-01
ECLASS 15.0	17-13-01-01		

## CRIMPFIX R VARIO

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Accessories / replacement parts



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

### General ordering data

Type	AIMESA CF U/L/LS SK TIN	Version	
Order No.	<a href="#">1283530000</a>	Automatic machines, Replacement part	
GTIN (EAN)	4050118073676		
Qty.	1 ST		

### Automatic machines



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

### General ordering data

Type	CRIMPFIX R VARIO PZ3	Version	
Order No.	<a href="#">2912420000</a>	Automatic machines, Automatic stripper and crimper	
GTIN (EAN)	4099986535992		
Qty.	1 ST		

### Accessories / replacement parts



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

### General ordering data

Type	FESA CF L/LS V2	Version	
Order No.	<a href="#">1454790000</a>	Automatic machines, Replacement part	
GTIN (EAN)	4050118260779		
Qty.	1 ST		