


**THM WO 20/32 WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

**General ordering data**

Version	THM, Conductor and cable markers, 2.8 - 7 mm, 20 x 32 mm, white
Order No.	<a href="#">262150000</a>
Type	THM WO 20/32 WS
GTIN (EAN)	4050118625547
Qty.	3000 items

## THM WO 20/32 WS

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	0.03 mm	Depth (inches)	0.001 inch
Height	20 mm	Height (inches)	0.7874 inch
Width	32 mm	Width (inches)	1.2598 inch
Net weight	0.12 g		

## Temperatures

Operating temperature range	-40...
-----------------------------	--------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## General data

Type of printing	neutral	
Version	Self-adhesive	
Width	32 mm	
UL 94 flammability rating	V-0	
Operating temperature range, min.	-40 °C	
Colour	white	
Halogen	No	
Printed characters	without	
Number of markers per packaging unit	Form of supply	Label reel
Size of labelling field	9 x 20 mm	
compatible printer	<a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a>	
Number of markers per combination	1 Label reel = Conductor and cable markers	
Operating temperature range	-40...	
Number per roll	3000	

## Conductor and cable markers

Halogen	No	Conductor O.D., max.	7 mm
Conductor O.D., min.	2.8 mm	Conductor O.D.	2.8 - 7 mm

## Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		



## THM WO 20/32 WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

### General ordering data

Type	RIBBON MM 110/360 SW	Version	
Order No.	<a href="#">2005070000</a>	Ink ribbon	
GTIN (EAN)	4050118390049		
Qty.	1 ST		