

**THM WO 50/100 SI****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

**General ordering data**

|            |  |
|------------|--|
| Version    | THM, Conductor and cable markers, 7 - 23 mm, 50 x 100 mm, silver |
| Order No.  | <a href="#">2596610000</a>                                       |
| Type       | THM WO 50/100 SI   |
| GTIN (EAN) | 4050118660852  |
| Qty.       | 1000 items   |

## THM WO 50/100 SI

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 0.03 mm | Depth (inches)  | 0.001 inch  |
| Height     | 50 mm   | Height (inches) | 1.9685 inch |
| Width      | 100 mm  | Width (inches)  | 3.937 inch  |
| Net weight | 0.75 g  |                 |             |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## General data

|                                      |  |            |
|--------------------------------------|--|------------|
| Adhesive                             | Polyacrylate adhesive                      |            |
| Orientation of print                 | horizontal and vertical                    |            |
| Type of printing                     | neutral                                    |            |
| Width                                | 100 mm                                     |            |
| UL 94 flammability rating            | V-0  |            |
| Colour                               | silver                                     |            |
| Halogen                              | No   |            |
| Basic material                       | Polyethylene                               |            |
| Printed characters                   | without                                    |            |
| Number of markers per packaging unit | Form of supply                             | Label reel |
| compatible printer                   |  |            |
| Number of markers per combination    | 1 Label reel = Conductor and cable markers |            |
| Number per roll                      | 1000                                       |            |

## Conductor and cable markers

|                      |           |                                  |                     |
|----------------------|-----------|----------------------------------|---------------------|
| Halogen              | No        | Conductor cross-section, max.    | 444 mm <sup>2</sup> |
| Conductor O.D., max. | 23 mm     | Conductor O.D., min.             | 7 mm                |
| Text field width     | 50 mm     | Text field height                | 25 mm               |
| Conductor O.D.       | 7 - 23 mm | Cross-section for connected wire | 444 mm <sup>2</sup> |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

**Drawings**

