

**EL 6 MM GE 30M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Customised identification: EL**

The endless variations of MultiMark markers make them an economical alternative to conventional tag rails or special labels. For any given width, the height can be precisely configured by the software to match the respective markers perfectly. A blade is used to cut the labels individually to the specified size. Perfect for producing large labels for function blocks or complete terminal blocks.

**Your benefits with MultiMark**

- “Different materials for various requirements”
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

**General ordering data**

|            |                                   |
|------------|-----------------------------------|
| Version    | THM, Device markers, 6 x , yellow |
| Order No.  | <a href="#">2621410000</a>        |
| Type       | EL 6 MM GE 30M                    |
| GTIN (EAN) | 4050118625639                     |
| Qty.       | 1 items                           |

## EL 6 MM GE 30M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Depth      | 0.1 mm   | Depth (inches)  | 0.0039 inch |
| Height     | 6 mm     | Height (inches) | 0.2362 inch |
| Length     | 30000 mm | Length (inches) | 1181.1 inch |
| Net weight | 50 g     |                 |             |

## Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...150 °C |
|-----------------------------|--------------|

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## General data

|                                   |                   |                                   |                                                                    |
|-----------------------------------|-------------------|-----------------------------------|--------------------------------------------------------------------|
| Adhesive                          | Acrylate adhesive | Version                           | halogen-free, Self-adhesive                                        |
| UL 94 flammability rating         | V-0               | Operating temperature range, max. | 150 °C                                                             |
| Operating temperature range, min. | -40 °C            | Colour                            | yellow                                                             |
| Halogen                           | No                | Length                            | 30000 mm                                                           |
| Basic material                    | Polyester         | Printed characters                | without                                                            |
| Approval acc. to UL 969           | Yes               | compatible printer                | <a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a> |
| Operating temperature range       | -40...150 °C      | Number per roll                   | 1                                                                  |

## Device markers

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ETIM 10.0   | EC001288    | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 |             |             |



## EL 6 MM GE 30M

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Ink ribbons




These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

#### General ordering data

|            |                            |            |  |
|------------|----------------------------|------------|--|
| Type       | RIBBON MM 76/360 SW        | Version    |  |
| Order No.  | <a href="#">2005080000</a> | Ink ribbon |  |
| GTIN (EAN) | 4050118389951              |            |  |
| Qty.       | 1 ST                       |            |  |

### THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.


#### General ordering data

|            |                            |         |  |
|------------|----------------------------|---------|--|
| Type       | THM MMP EXT.RH             | Version |  |
| Order No.  | <a href="#">1302920000</a> |         |  |
| GTIN (EAN) | 4050118102307              |         |  |
| Qty.       | 1 ST                       |         |  |

|            |                            |         |  |
|------------|----------------------------|---------|--|
| Type       | MULTIMARK ROLLER 115       | Version |  |
| Order No.  | <a href="#">1357420000</a> |         |  |
| GTIN (EAN) | 4050118160314              |         |  |
| Qty.       | 1 ST                       |         |  |

### THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

## Accessories

### General ordering data

|            |                            |         |
|------------|----------------------------|---------|
| Type       | MULTIMARK PLUS ROLLER 1... | Version |
| Order No.  | <a href="#">2672590000</a> |         |
| GTIN (EAN) | 4050118708097              |         |
| Qty.       | 1 ST                       |         |