

THM WO 24/69 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 5 - 16 mm, 24 x 69 mm, white
Order No.	2621520000
Type	THM WO 24/69 WS
GTIN (EAN)	4050118625523
Qty.	1000 items

THM WO 24/69 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	0.03 mm	Depth (inches)	0.001 inch
Height	24 mm	Height (inches)	0.9449 inch
Width	69 mm	Width (inches)	2.7165 inch
Net weight	0.2 g		

Temperatures

Operating temperature range -40...

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Type of printing	neutral		
Version	Self-adhesive		
Width	69 mm		
UL 94 flammability rating	V-0		
Operating temperature range, min.	-40 °C		
Colour	white		
Halogen	No		
Printed characters	without		
Number of markers per packaging unit	Form of supply	Label reel	
Size of labelling field	16 x 24 mm		
compatible printer	THM MULTIMARK , THM MULTIMARK PLUS		
Number of markers per combination	1 Label reel = Conductor and cable markers		
Operating temperature range	-40...		
Number per roll	1000		


Conductor and cable markers

Halogen	No	Conductor O.D., max.	16 mm
Conductor O.D., min.	5 mm	Conductor O.D.	5 - 16 mm

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

Drawings



THM WO 24/69 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Accessories

www.weidmueller.com

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 110/360 SW	Version	
Order No.	2005070000	Ink ribbon	
GTIN (EAN)	4050118390049		
Qty.	1 ST		