

POWERCRIMPER 6.0**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The rationalisation of crimping processes calls for more and more automation of the individual steps. "Optimisation of installation times" is what the markets of the future will be demanding of their strategic partners. Automatic machines that permit rational processing of conductor materials represent the answer to an approach geared to future needs. Versatility and functionality are decisive factors for the customer. With our comprehensive line of automated machinery, Weidmüller provides professional and efficient solutions for cable preparation and processing.

General ordering data

Version	Crimping machine, 0.5mm ² , 6mm ²
Order No.	2634310000
Type	POWERCRIMPER 6.0
GTIN (EAN)	4050118660906
Qty.	1 items

POWERCRIMPER 6.0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	405 mm	Depth (inches)	15.9449 inch
Height	240 mm	Height (inches)	9.4488 inch
Width	165 mm	Width (inches)	6.4961 inch
Net weight	12500 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	d2df479e-2b79-4e98-adc7-b03577df98ae

Automatic crimping

Drive	Electropneumatic	Pulse time	approx. 1 s
Wire end ferrules cross-section, max.	6 mm ²	Wire end ferrules cross-section, min.	0.5 mm ²
Crimping range, max.	6 mm ²	Crimping range, min.	0.5 mm ²
Crimping length	6 - 18 mm	Consumables	With and without plastic collar, Twin wire-end ferrules
Compressed-air connection	5 - 5.5 bar	Electrical connection	100 - 240 V / 50/60 Hz / 16 VA
Note	Twin wire-end ferrules in the cross-section range from 2 x 0.5 to 2 x 2.5 mm ² , No need to change tools	Insertion length	13
Crimping range	0.5...6 mm ²		

Classifications

ETIM 8.0	EC002778	ETIM 9.0	EC002778
ETIM 10.0	EC002778	ECLASS 14.0	17-13-01-01
ECLASS 15.0	17-13-01-01		

POWERCRIMPER 6.0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

