

**HDC MHP70 M 25**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

**General ordering data**

|            |                                       |
|------------|---------------------------------------|
| Version    | Male, silver, 25 - 25 mm <sup>2</sup> |
| Order No.  | <a href="#">2668370000</a>            |
| Type       | HDC MHP70 M 25                        |
| GTIN (EAN) | 4050118803013                         |
| Qty.       | 10 items                              |

**HDC MHP70 M 25**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Net weight 10.8 g

**Environmental Product Compliance**

RoHS Compliance Status Compliant with exemption  
 RoHS Exemption (if applicable/known) 6c  
 REACH SVHC Lead 7439-92-1  
 SCIP 6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

**General data**

|                                  |                         |                                    |                    |
|----------------------------------|-------------------------|------------------------------------|--------------------|
| Contact diameter, male Ø         | 6 mm                    | Stripping length, rated connection | 16 mm              |
| Type of connection               | Crimp connection        | Version insert                     | MHP                |
| Conductor cross-section, max.    | 25 mm <sup>2</sup>      | Conductor cross-section, min.      | 25 mm <sup>2</sup> |
| Surface finish                   | silver                  | Plugging cycles                    | ≥ 500              |
| Type                             | Male                    | Basic material                     | Copper alloy       |
| Series                           | ModuPlug                | Production methods                 | turned             |
| Cross-section for connected wire | 25 - 25 mm <sup>2</sup> |                                    |                    |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000796    | ETIM 9.0    | EC000796    |
| ETIM 10.0   | EC000796    | ECLASS 14.0 | 27-44-02-04 |
| ECLASS 15.0 | 27-44-02-04 |             |             |

**HDC MHP70 M 25**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

