

TC INL THIRD 6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Inspired by 5S and lean management methods, Weidmüller foam inserts ensure an efficient and tidy workplace. Designed according to a modular principle, they offer many advantages and can be selected according to individual requirements.

General ordering data

Order No.	2683840000
Type	TC INL THIRD 6
GTIN (EAN)	4050118701951
Qty.	1 items

TC INL THIRD 6

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	50 mm	Depth (inches)	1.9685 inch
Height	446 mm	Height (inches)	17.559 inch
Width	200 mm	Width (inches)	7.874 inch
Net weight	1259 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

Technical data

Description of article	Foam inlay socket set
------------------------	-----------------------

Tool chest

Assembly	with tools
----------	------------

Classifications

ETIM 6.0	EC011819	ETIM 7.0	EC011819
ETIM 8.0	EC011819	ETIM 9.0	EC011819
ETIM 10.0	EC011819	ECLASS 9.1	21-07-92-03
ECLASS 10.0	21-07-92-03	ECLASS 11.0	21-07-04-12
ECLASS 12.0	21-07-04-12	ECLASS 13.0	21-07-04-12
ECLASS 14.0	21-07-04-12	ECLASS 15.0	21-07-04-12

Accessories

Screwty® cable gland tool



The ideal tool for any application

Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

Type	SCREWTY SET	Version
Order No.	1910000000	Cable gland tool for M8, M12 lines and connectors
GTIN (EAN)	4032248436842	
Qty.	1 ST	

Cable gland tools



Screwing tool for fixing and loosening cable glands and accessories in the sizes 11-36 AF.

- Can reach over several rows of glands
- No deforming of the cable glands
- Spanner size 11 to 36 mm
- Infinite adjustment of spanner size
- Ratchet function: not necessary to remove tool between turns
- Authentic one-hand tool

General ordering data

Type	FLECAFIX 11/24	Version
Order No.	9015900000	Cable gland tool
GTIN (EAN)	4032248309573	
Qty.	1 ST	
Type	FLECAFIX 24/36	Version
Order No.	9015980000	Cable gland tool
GTIN (EAN)	4032248309597	
Qty.	1 ST	