

HDC MXCC10 4X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



In addition to heavy-duty connectors, RockStar® includes the appropriate accessories for effective, functional and safe system cabling; e.g. coding systems, shield clamps, cover plates and replacement seals

General ordering data

Version	Cross-connector bridge, Heavy duty connector assemblies
Order No.	2709800000
Type	HDC MXCC10 4X
GTIN (EAN)	4050118805741
Qty.	20 items

HDC MXCC10 4X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Net weight 7.03 g

Temperatures

Limit temperature -40 °C ... 125 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Version For ModuPlug MHE 4X module Basic material PA 66/6

Classifications

ETIM 8.0	EC002943	ETIM 9.0	EC002943
ETIM 10.0	EC002943	ECLASS 14.0	27-44-02-92
ECLASS 15.0	27-44-02-92		

HDC MXCC10 4X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Electrical modules



Flexible

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

General ordering data

Type	HDC MHE 4X FP	Version
Order No.	2636060000	Signal module, 250 V, 16 A, Number of poles: 4, PUSH IN with actuator, Female, Required plug-in slots: 0.5
GTIN (EAN)	4050118692808	
Qty.	1 ST	
Type	HDC MHE 4X MP	Version
Order No.	2636070000	Signal module, 250 V, 16 A, Number of poles: 4, PUSH IN with actuator, Pin, Required plug-in slots: 0.5
GTIN (EAN)	4050118692815	
Qty.	1 ST	
Type	HDC MHE 4X2 FP	Version
Order No.	2636080000	Signal module, 250 V, 16 A, Number of poles: 4, PUSH IN with actuator, Female, Required plug-in slots: 0.5
GTIN (EAN)	4050118692822	
Qty.	1 ST	
Type	HDC MHE 4X2 MP	Version
Order No.	2636090000	Signal module, 250 V, 16 A, Number of poles: 4, PUSH IN with actuator, Pin, Required plug-in slots: 0.5
GTIN (EAN)	4050118692839	
Qty.	1 ST	