

**HDC 24B TSS 1M40 WMP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Our flange-mounted housings made of plastic have a built-in cable gland and a screw interlock. They seal directly onto the panel wall and can therefore be used without an attachment housing. The housings are impressive with their low weight and optimal protection against contamination, water and vibrations.

**General ordering data**

Version	HDC enclosures, Installation size: 8, Protection degree: IP66, IP67, in plugged condition, Cable entry from side, Screw, , Size of cable entries: M 40
Order No.	<a href="#">2716780000</a>
Type	HDC 24B TSS 1M40 WMP
GTIN (EAN)	4050118803655
Qty.	1 items

## HDC 24B TSS 1M40 WMP

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E223801

## Dimensions and weights

Net weight 185.68 g

## Temperatures

Ambient temperature -40 °C...100 °C

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

## Cable Gland WMP

Cable diameter, min. 19 mm Cable diameter, max. 28 mm

AF size 36 mm Size of cable entries M 40

## Dimensions

Cable entry w. cable glands

## General data

UL 94 flammability rating V-0 Surface finish untreated

Protection degree IP66, IP67, in plugged condition

## Version

Number of cable glands	1	Size of cable entries	M 40
Top part/bottom part/lid	upper part	Cover	without cover
Tightening torque	3 Nm	Number of cable entry sideways	1
Design of housing	Cable entry from side	Design of locking system	Screw
Installation size	8	Cable entry	w. cable glands
Sealing	NBR	Colour (RAL)	RAL 9011
BG	8	Suitable for ModuPlug®	Yes

## Classifications

ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		

**HDC 24B TSS 1M40 WMP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

