

**HDC MMARK 4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

In addition to heavy-duty connectors, RockStar® includes the appropriate accessories for effective, functional and safe system cabling; e.g. coding systems, shield clamps, cover plates and replacement seals

**General ordering data**

Version	Marking tags, Heavy duty connector assemblies
Order No.	<a href="#">2710590000</a>
Type	HDC MMARK 4
GTIN (EAN)	4050118783902
Qty.	640 items

## HDC MMARK 4

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Width	3.1 mm	Width (inches)	0.122 inch
Net weight	0.17 g		

### Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Version	For ModuPlug MHE 4X module	Basic material	PA 66, POM
---------	----------------------------	----------------	------------

### General data

Orientation of print	horizontal	Version	For ModuPlug MHE 4X module
Width	3.1 mm	UL 94 flammability rating	V-2, HB
Operating temperature range, max.	125 °C	Operating temperature range, min.	-40 °C
Colour	white	Basic material	PA 66, POM
Printed characters	neutral	compatible printer	<a href="#">MCP BASIC 2</a> , <a href="#">MCP PLUS 2</a>

### Classifications

ETIM 8.0	EC000761	ETIM 9.0	EC000761
ETIM 10.0	EC000761	ECLASS 14.0	27-28-11-01
ECLASS 15.0	27-28-11-01		



## HDC MMARK 4

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Electrical modules



## Flexible

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

## General ordering data

Type	HDC MHE 4X FP	Version
Order No.	<a href="#">2636060000</a>	Signal module, 250 V, 16 A, Number of poles: 4, PUSH IN with actuator, Female, Required plug-in slots: 0.5
GTIN (EAN)	4050118692808	
Qty.	1 ST	
Type	HDC MHE 4X MP	Version
Order No.	<a href="#">2636070000</a>	Signal module, 250 V, 16 A, Number of poles: 4, PUSH IN with actuator, Pin, Required plug-in slots: 0.5
GTIN (EAN)	4050118692815	
Qty.	1 ST	
Type	HDC MHE 4X2 FP	Version
Order No.	<a href="#">2636080000</a>	Signal module, 250 V, 16 A, Number of poles: 4, PUSH IN with actuator, Female, Required plug-in slots: 0.5
GTIN (EAN)	4050118692822	
Qty.	1 ST	
Type	HDC MHE 4X2 MP	Version
Order No.	<a href="#">2636090000</a>	Signal module, 250 V, 16 A, Number of poles: 4, PUSH IN with actuator, Pin, Required plug-in slots: 0.5
GTIN (EAN)	4050118692839	
Qty.	1 ST	