

HDC MMARK 4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

In addition to heavy-duty connectors, RockStar® includes the appropriate accessories for effective, functional and safe system cabling; e.g. coding systems, shield clamps, cover plates and replacement seals

General ordering data

Version	Marking tags, Heavy duty connector assemblies
Order No.	2710590000
Type	HDC MMARK 4
GTIN (EAN)	4050118783902
Qty.	640 items

HDC MMARK 4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Width	3.1 mm	Width (inches)	0.122 inch
Net weight	0.17 g		

Temperatures

Limit temperature -40 °C ... 125 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Version	For ModuPlug MHE 4X module	Basic material	PA 66, POM
---------	----------------------------	----------------	------------

General data

Orientation of print	horizontal	Version	For ModuPlug MHE 4X module
Width	3.1 mm	UL 94 flammability rating	V-2, HB
Operating temperature range, max.	125 °C	Operating temperature range, min.	-40 °C
Colour	white	Basic material	PA 66, POM
Printed characters	neutral	compatible printer	MCP BASIC 2 , MCP PLUS 2

Classifications

ETIM 8.0	EC000761	ETIM 9.0	EC000761
ETIM 10.0	EC000761	ECLASS 14.0	27-28-11-01
ECLASS 15.0	27-28-11-01		

HDC MMARK 4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Electrical modules



Flexible

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

General ordering data

Type	HDC MHE 4X FP	Version
Order No.	2636060000	Signal module, 250 V, 16 A, Number of poles: 4, PUSH IN with actuator, Female, Required plug-in slots: 0.5
GTIN (EAN)	4050118692808	
Qty.	1 ST	
Type	HDC MHE 4X MP	Version
Order No.	2636070000	Signal module, 250 V, 16 A, Number of poles: 4, PUSH IN with actuator, Pin, Required plug-in slots: 0.5
GTIN (EAN)	4050118692815	
Qty.	1 ST	
Type	HDC MHE 4X2 FP	Version
Order No.	2636080000	Signal module, 250 V, 16 A, Number of poles: 4, PUSH IN with actuator, Female, Required plug-in slots: 0.5
GTIN (EAN)	4050118692822	
Qty.	1 ST	
Type	HDC MHE 4X2 MP	Version
Order No.	2636090000	Signal module, 250 V, 16 A, Number of poles: 4, PUSH IN with actuator, Pin, Required plug-in slots: 0.5
GTIN (EAN)	4050118692839	
Qty.	1 ST	