

HSS 12.7-38.1 EL OR30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

Version	Conductor and cable markers, 12.7 - 38.1 mm, orange
Order No.	2712010000
Type	HSS 12.7-38.1 EL OR30M
GTIN (EAN)	4050118749922
Qty.	1 items

HSS 12.7-38.1 EL OR30M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.77 mm	Depth (inches)	0.0303 inch
Width	60.5 mm	Width (inches)	2.3819 inch
Length	30000 mm	Length (inches)	1181.1 inch
Net weight	500 g		

Temperatures

Operating temperature range	-55...135 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Type of printing	neutral	Width	60.5 mm
Operating temperature range, max.	135 °C	Operating temperature range, min.	-55 °C
Colour	orange	Halogen	Yes
Length	30000 mm	Basic material	Polyolefine
Printed characters	without	Recommended industries	Plant manufacture, Energy, Device manufacturer, Machinery
compatible printer	THM MULTIMARK , THM MULTIMARK PLUS	Operating temperature range	-55...135 °C

Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	240 mm ²
Conductor cross-section, min.	35 mm ²	Conductor O.D., max.	38.1 mm
Conductor O.D., min.	12.7 mm	Rate of shrinkage	3:1
Recommended shrinking temperature	90 °C	Conductor O.D.	12.7 - 38.1 mm
Cross-section for connected wire	35 - 240 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

HSS 12.7-38.1 EL OR30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Ink ribbons




These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON HSS HF EL 40/300...	Version	
Order No.	1426210000	Ink ribbon	
GTIN (EAN)	4050118228823		
Qty.	1 ST		

THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	THM MMP EXT.RH	Version	
Order No.	1302920000		
GTIN (EAN)	4050118102307		
Qty.	1 ST		