

HDC 24B TOS 1M40 WMP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Our flange-mounted housings made of plastic have a built-in cable gland and a screw interlock. They seal directly onto the panel wall and can therefore be used without an attachment housing. The housings are impressive with their low weight and optimal protection against contamination, water and vibrations.

General ordering data

Version	HDC enclosures, Installation size: 8, Protection degree: IP66, IP67, in plugged condition, Cable entry from top, Screw, , Size of cable entries: M 40
Order No.	2716740000
Type	HDC 24B TOS 1M40 WMP
GTIN (EAN)	4050118803617
Qty.	1 items

HDC 24B TOS 1M40 WMP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E223801

Dimensions and weights

Net weight 185.68 g

Temperatures

Ambient temperature -40 °C...100 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

Cable Gland WMP

Cable diameter, min. 19 mm Cable diameter, max. 28 mm

AF size 36 mm Size of cable entries M 40

Dimensions

Cable entry w. cable glands

General data

UL 94 flammability rating V-0 Surface finish untreated

Protection degree IP66, IP67, in plugged condition

Version

Number of cable glands 1 Size of cable entries M 40

Top part/bottom part/lid upper part Cover without cover

Tightening torque 3 Nm Number of cable entry on top 1

Number of cable entry sideways 1 Design of housing Cable entry from top

Design of locking system Screw Installation size 8

Cable entry w. cable glands Sealing NBR

Colour (RAL) RAL 9011 BG 8

Suitable for ModuPlug® Yes

Classifications

ETIM 8.0 EC000437 ETIM 9.0 EC000437

ETIM 10.0 EC000437 ECLASS 14.0 27-44-02-02



ECLASS 15.0 27-44-02-02

HDC 24B TOS 1M40 WMP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



HDC 24B TOS 1M40 WMP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

Mounting brackets



Our flange-mounted housings made of plastic have a built-in cable gland and a screw interlock. They seal directly onto the panel wall and can therefore be used without an attachment housing. The housings are impressive with their low weight and optimal protection against contamination, water and vibrations.

General ordering data

Type	HDC AF SET WM	Version	
Order No.	2716800000	HDC enclosures, Installation size: , Protection degree:	
GTIN (EAN)	4050118803679		
Qty.	1 ST		
Type	HDC AF WM	Version	
Order No.	2716790000	HDC enclosures, Installation size: , Protection degree:	
GTIN (EAN)	4050118803662		
Qty.	20 ST		