

THM MT30X 15/4 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

General ordering data

| | |
|------------|---------------------------------------|
| Version | THM, Device markers, 4 x 15 mm, white |
| Order No. | 2799200000 |
| Type | THM MT30X 15/4 WS |
| GTIN (EAN) | 4064675260936 |
| Qty. | 10000 items |

THM MT30X 15/4 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 0.08 mm | Depth (inches) | 0.0031 inch |
| Height | 4 mm | Height (inches) | 0.1575 inch |
| Width | 15 mm | Width (inches) | 0.5906 inch |
| Net weight | 0.01 g | | |

Temperatures

Operating temperature range -40...150 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

| | | | |
|---|-------------------------------|------------|--|
| Adhesive | Acrylate | | |
| Version | Self-adhesive | | |
| Width | 15 mm | | |
| UL 94 flammability rating | V-0 | | |
| Operating temperature range, max. | 150 °C | | |
| Operating temperature range, min. | -40 °C | | |
| Colour | white | | |
| Halogen | No | | |
| Basic material | Polyester | | |
| Printed characters | without | | |
| Number of markers per packaging unit compatible printer | Form of supply | Label reel | |
| Number of markers per combination | 1 Label reel = Device markers | | |
| Operating temperature range | -40...150 °C | | |

Device markers

Halogen No

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ETIM 10.0 | EC001288 | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 | | |

THM MT30X 15/4 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

