

**SDIS SLIM 1.2X6.5X150****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

**General ordering data**

|            |                                                                                           |
|------------|-------------------------------------------------------------------------------------------|
| Version    | Mounting tool, Blade width (B): 6.5 mm, Blade length: 150 mm, Blade thickness (A): 1.2 mm |
| Order No.  | <a href="#">2749640000</a>                                                                |
| Type       | SDIS SLIM 1.2X6.5X150                                                                     |
| GTIN (EAN) | 4050118896381                                                                             |
| Qty.       | 1 items                                                                                   |

**SDIS SLIM 1.2X6.5X150**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Approvals**

Approvals

**Dimensions and weights**

|          |        |                 |             |
|----------|--------|-----------------|-------------|
| Length   | 265 mm | Length (inches) | 10.433 inch |
| Diameter | 6.5 mm | Net weight      | 102.96 g    |

**Environmental Product Compliance**

|                        |                       |
|------------------------|-----------------------|
| RoHS Compliance Status | Not affected          |
| REACH SVHC             | No SVHC above 0.1 wt% |

**Technical data**

|                        |                                                                       |         |          |
|------------------------|-----------------------------------------------------------------------|---------|----------|
| Description of article | VDE-insulated screwdriver with slotted blade<br>1.2x6.5x150, SlimLine | Version | straight |
|------------------------|-----------------------------------------------------------------------|---------|----------|

**Screwing tools**

|                 |         |                     |        |
|-----------------|---------|---------------------|--------|
| Blade width (B) | 6.5 mm  | Blade thickness (A) | 1.2 mm |
| Form            | Slotted | Blade length        | 150 mm |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000158    | ETIM 9.0    | EC000158    |
| ETIM 10.0   | EC000158    | ECLASS 14.0 | 21-04-04-07 |
| ECLASS 15.0 | 21-04-04-07 |             |             |