

## IE-USB-A-C-2.0M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Assembled IE cables

### General ordering data

|            |                                   |
|------------|-----------------------------------|
| Version    | USB cable, USB A, USB C, PVC, 2 m |
| Order No.  | <a href="#">2838380020</a>        |
| Type       | IE-USB-A-C-2.0M                   |
| GTIN (EAN) | 4064675444329                     |
| Qty.       | 1 items                           |

## IE-USB-A-C-2.0M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

|            |         |                 |              |
|------------|---------|-----------------|--------------|
| Length     | 2 m     | Length (inches) | 78.7402 inch |
| Net weight | 50.16 g |                 |              |

## Temperatures

|                          |                       |                |
|--------------------------|-----------------------|----------------|
| Storage temperature      | Operating temperature | -15 °C...80 °C |
| Installation temperature |                       |                |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Technical specifications for cable

|                  |       |
|------------------|-------|
| Sheathing colour | black |
|------------------|-------|

## Cable structure

|                       |        |                       |        |
|-----------------------|--------|-----------------------|--------|
| Sheathing colour      | black  | Sheath diameter, max. | 3.9 mm |
| Sheath diameter, min. | 3.5 mm | Material sheath       | PVC    |

## Plug, left

|           |                                                              |
|-----------|--------------------------------------------------------------|
| Plug left | USB A, IP20, male contact, straight, plug, Plastic, shielded |
|-----------|--------------------------------------------------------------|

## Plug, right

|            |                                                       |
|------------|-------------------------------------------------------|
| Plug right | IP20, male contact, straight, plug, Plastic, shielded |
|------------|-------------------------------------------------------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001408    | ETIM 9.0    | EC001408    |
| ETIM 10.0   | EC001408    | ECLASS 14.0 | 27-06-01-06 |
| ECLASS 15.0 | 27-06-01-06 |             |             |