

FSPG LED 30-70V BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The fuse holder SIHA quickly turns a disconnect terminal into a fuse terminal: simply remove the disconnect lever and attach the fuse unit.

General ordering data

| | |
|------------|---|
| Version | Fuse holder for feed-through modular terminal, black, 6.3 A, Pivoting, V-0, Wemid |
| Order No. | 2869710000 |
| Type | FSPG LED 30-70V BK |
| GTIN (EAN) | 4064675623823 |
| Qty. | 25 items |

FSPG LED 30-70V BK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 38 mm | Depth (inches) | 1.4961 inch |
| Height | 36.5 mm | Height (inches) | 1.437 inch |
| Width | 6 mm | Width (inches) | 0.2362 inch |
| Net weight | 5.35 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|--------|
| Ambient temperature | -60 °C...85 °C | Continuous operating temp., min. | -60 °C |
| Continuous operating temp., max. | 130 °C | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|----------------|-------|---------------------------|-------|
| Basic material | Wemid | Insulating material | Wemid |
| Colour | black | UL 94 flammability rating | V-0 |

System specifications

| | |
|--------------------------|----|
| End cover plate required | No |
|--------------------------|----|

Additional technical data

| | |
|------------------|---------|
| Type of mounting | Plugged |
|------------------|---------|

Rating data

| | |
|--------------------|---|
| Pollution severity | 3 |
|--------------------|---|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002848 | ETIM 9.0 | EC002848 |
| ETIM 10.0 | EC002848 | ECLASS 14.0 | 27-25-03-90 |
| ECLASS 15.0 | 27-25-03-90 | | |

FSPG LED 30-70V BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

