

## BIT E6,3 T20 X 150

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



The Weidmüller bits are standard bits which are highly popular with users thanks to their good quality, large range and efficiency. The computer-controlled hardening method enables Weidmüller to guarantee a consistently high standard of quality.

The high-quality raw materials used make it possible to reach torques far higher than any of those specified in the relevant DIN standards:

- DIN 5261 for PH/PZ bits,
- DIN 5263 for slotted bits,
- Camcar standard for TORX bits

That means a long life at high torques and hence ideal conditions for standard situations.

The benefits:

- Suitable for all types of screws. Because of their excellent hardness values of 59-61 HRC, they are suitable for use with both manual and power tools.
- Good wearing resistance and thus a long life expectancy.
- Optimum fit in all DIN screws means low wear and optimum torque transmission.
- Manufactured to meet professional quality criteria according to relevant ISO standards with a consistently high standard of quality.

### General ordering data

|            |                            |
|------------|----------------------------|
| Version    | Mounting tool              |
| Order No.  | <a href="#">2821510000</a> |
| Type       | BIT E6,3 T20 X 150         |
| GTIN (EAN) | 4064675359050              |
| Qty.       | 5 items                    |

**BIT E6,3 T20 X 150**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Dimensions and weights**

|            |        |                |             |
|------------|--------|----------------|-------------|
| Width      | 150 mm | Width (inches) | 5.9055 inch |
| Net weight | 20 g   |                |             |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**Screwing tools**

|      |      |      |     |
|------|------|------|-----|
| Form | Torx | Size | T20 |
|------|------|------|-----|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC003864    | ETIM 9.0    | EC003864    |
| ETIM 10.0   | EC003864    | ECLASS 14.0 | 21-04-42-02 |
| ECLASS 15.0 | 21-04-42-02 |             |             |