

CRIMPFIX ECO



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

| | |
|------------|--|
| Version | Automatic machines, Automatic stripper and crimper |
| Order No. | 2833890000 |
| Type | CRIMPFIX ECO |
| GTIN (EAN) | 4064675422570 |
| Qty. | 1 items |

CRIMPFIX ECO

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|--------------|
| Depth | 323 mm | Depth (inches) | 12.7165 inch |
| Height | 188 mm | Height (inches) | 7.4016 inch |
| Width | 230 mm | Width (inches) | 9.0551 inch |
| Net weight | 12496 g | | |

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c, 7a, 7cI |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | d2df479e-2b79-4e98-adc7-b03577df98ae |

PW65 maintenance - automatic stripping/crimping

| | | | |
|---------------------------------------|---|---------------------------------------|-------------------------------|
| Stripping range | 0.5 - 2.5 mm ² (~ AWG 20-14) | Drive | Electro-mechanical |
| Pulse time | approx. 1.5 s | Crimping | Trapezoidal |
| Wire end ferrules cross-section, max. | 2.5 mm ² | Wire end ferrules cross-section, min. | 0.5 mm ² |
| Crimping range, max. | 2.5 mm ² | Crimping range, min. | 0.5 mm ² |
| Crimping length | 8 mm | Consumables | Linked wire-end ferrules |
| Length of wire-end ferrule | 14 mm | Electrical connection | 100-240 V / 50/60 Hz / 100 VA |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002778 | ETIM 9.0 | EC002778 |
| ETIM 10.0 | EC002778 | ECLASS 14.0 | 17-13-01-01 |
| ECLASS 15.0 | 17-13-01-01 | | |

CRIMPFIX ECO

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Accessories / replacement parts



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

| | | | |
|------------|-------------------------------|--------------------------------------|--|
| Type | AIMESA CF ECO | Version | |
| Order No. | 2875560000 | Automatic machines, Replacement part | |
| GTIN (EAN) | 4064675654674 | | |
| Qty. | 1 ST | | |
| Type | HUELSENTRENNMESSER CRIM... | Version | |
| Order No. | 2875570000 | Automatic machines, Replacement part | |
| GTIN (EAN) | 4064675654681 | | |
| Qty. | 1 ST | | |