

## CRIMPFIX ECO

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

### General ordering data

Version	Automatic machines, Automatic stripper and crimper
Order No.	<a href="#">2833890000</a>
Type	CRIMPFIX ECO
GTIN (EAN)	4064675422570
Qty.	1 items

## CRIMPFIX ECO

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	323 mm	Depth (inches)	12.7165 inch
Height	188 mm	Height (inches)	7.4016 inch
Width	230 mm	Width (inches)	9.0551 inch
Net weight	12496 g		

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cI
REACH SVHC	Lead 7439-92-1
SCIP	d2df479e-2b79-4e98-adc7-b03577df98ae

## PW65 maintenance - automatic stripping/crimping

Stripping range	0.5 - 2.5 mm <sup>2</sup> (~ AWG 20-14)	Drive	Electro-mechanical
Pulse time	approx. 1.5 s	Crimping	Trapezoidal
Wire end ferrules cross-section, max.	2.5 mm <sup>2</sup>	Wire end ferrules cross-section, min.	0.5 mm <sup>2</sup>
Crimping range, max.	2.5 mm <sup>2</sup>	Crimping range, min.	0.5 mm <sup>2</sup>
Crimping length	8 mm	Consumables	Linked wire-end ferrules
Length of wire-end ferrule	14 mm	Electrical connection	100-240 V / 50/60 Hz / 100 VA

## Classifications

ETIM 8.0	EC002778	ETIM 9.0	EC002778
ETIM 10.0	EC002778	ECLASS 14.0	17-13-01-01
ECLASS 15.0	17-13-01-01		

**CRIMPFIX ECO**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Accessories**

**Accessories / replacement parts**



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

**General ordering data**

Type	AIMESA CF ECO	Version	
Order No.	<a href="#">2875560000</a>	Automatic machines, Replacement part	
GTIN (EAN)	4064675654674		
Qty.	1 ST		
Type	HUELSENTRENNMESSER CRIM...	Version	
Order No.	<a href="#">2875570000</a>	Automatic machines, Replacement part	
GTIN (EAN)	4064675654681		
Qty.	1 ST		