

## RC M P2 M20 SP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The circular connectors with screw system are characterised by their compact design. This allows them to be used in a wide range of applications and industries. They are available both as plugs and sockets.

### General ordering data

Order No.	2860650000
Type	<a href="#">RC M P2 M20 SP</a>
GTIN (EAN)	4064675576662

## RC M P2 M20 SP

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E307231

## Dimensions and weights

Diameter	20 mm	Net weight	12 g
----------	-------	------------	------

## Temperatures

Storage temperature		Ambient temperature	-25 °C...125 °C
Operating temperature	-40 °C...85 °C		

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	b64e9137-212c-40f4-8b4a-2cb7feb25f72

## Technical data customisable plug-in connectors

Number of poles	2	Coding	none
Contact surface	Brass	LED	No
Type of connection	Screw connection	Housing main material	PA 66
Cable diameter, max.	13 mm	Cable diameter, min.	7 mm
Contact material	Brass	Conductor cross-section, max.	4 mm <sup>2</sup>
Conductor cross-section, min.	0.5 mm <sup>2</sup>	Nominal voltage	500 V
Nominal current	17.5 A	Protection degree	IP68
Gender of contact	Male	Shield connection	No
Threaded ring material	Plastic	Connection cross-section, max.	4 mm <sup>2</sup>
Connection cross-section, min.	0.5 mm <sup>2</sup>		

## General data

Number of poles	2	Connection thread	M20
Reverse polarity protection	Yes	Type of connection	Screw connection
Housing main material	PA 66		

## Classifications

ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		

## RC M P2 M20 SP

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Round connector M20 mounting tool



**Tool:**  
 This tool is ideal for installing the M20 built-in connectors.

#### General ordering data

Type	MTA RC	Version
Order No.	<a href="#">2884950000</a>	
GTIN (EAN)	4064675852070	
Qty.		

### Plug connector - screw system



The circular connectors with screw system are characterised by their compact design. This allows them to be used in a wide range of applications and industries. They are available both as plugs and sockets.

#### General ordering data

Type	RC F P2 SP	Version
Order No.	<a href="#">2903200000</a>	
GTIN (EAN)	4099986122376	
Qty.		

### M20

Protective caps suitable for FieldPower and WIPL family with round connector



#### General ordering data

Type	PC RC M	Version
Order No.	<a href="#">2820090000</a>	
GTIN (EAN)	4064675591405	
Qty.		