

**CC 74/101 MM WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Standard included: CC

Our systematically matching product range includes labels for identifying standardised components, as well as all-purpose and familiar formats such as the CC 85/54 marker for nameplates.

Your benefits with MultiMark

- “Different materials for various requirements”
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

**General ordering data**

|            |                                              |
|------------|----------------------------------------------|
| Version    | ClipCard, Device markers, 74 x 101 mm, white |
| Order No.  | <a href="#">2885750000</a>                   |
| Type       | CC 74/101 MM WS                              |
| GTIN (EAN) | 4064675854357                                |
| Qty.       | 250 items                                    |

## CC 74/101 MM WS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 0.1 mm | Depth (inches)  | 0.0039 inch |
| Height     | 74 mm  | Height (inches) | 2.9134 inch |
| Width      | 101 mm | Width (inches)  | 3.9764 inch |
| Net weight | 1.89 g |                 |             |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## General data

|                                   |                   |                                   |               |
|-----------------------------------|-------------------|-----------------------------------|---------------|
| Adhesive                          | Acrylate adhesive | Version                           | Self-adhesive |
| Width                             | 101 mm            | UL 94 flammability rating         | V-0           |
| Operating temperature range, max. | 120 °C            | Operating temperature range, min. | -40 °C        |
| Colour                            | white             | Halogen                           | No            |
| Basic material                    | Polyester         | Printed characters                | neutral       |

## Device markers

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ETIM 10.0   | EC001288    | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 |             |             |