

THM MULTIMARK TWIN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Version	Marking systems, Thermotransfer, 300 DPI, Shrink-fit sleeves
Order No.	2931860000
Type	THM MULTIMARK TWIN
GTIN (EAN)	4099986669895
Qty.	1 items

THM MULTIMARK TWIN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	395 mm	Depth (inches)	15.5511 inch
Height	544 mm	Height (inches)	21.4173 inch
Width	248 mm	Width (inches)	9.7638 inch
Net weight	21000 g		

Temperatures

Humidity 10...85% (no condensation)

Environmental Product Compliance

RoHS Compliance Status Compliant
 REACH SVHC Lead 7439-92-1

Labelling systems

Marker type	Shrink-fit sleeves	Memory (RAM)	256 MB
Printing method	Thermotransfer	Interface	LAN, USB 2.0
Software	M-Print® PRO	Type	THM TwinMark printer
Supply voltage	100...240 V AC	Operating system	Windows 7, Windows 8, Windows 8.1, Windows 10, Windows 11
Printing speed	max. 150 mm/s	Print resolution, max.	300 DPI

Classifications

ETIM 8.0	EC000610	ETIM 9.0	EC000610
ETIM 10.0	EC000610	ECLASS 14.0	24-32-11-90
ECLASS 15.0	24-32-11-90		

THM MULTIMARK TWIN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Ink ribbons




These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON HSS HF EL 40/300...	Version
Order No.	1426210000	Ink ribbon
GTIN (EAN)	4050118228823	
Qty.	1 ST	

Type	RIBBON MM-HS 60/300 SW	Version
Order No.	2448880000	Ink ribbon
GTIN (EAN)	4050118462944	
Qty.	1 ST	

THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	MULTIMARK PLUS ROLLER 1...	Version
Order No.	2672590000	
GTIN (EAN)	4050118708097	
Qty.	1 ST	

Type	MULTIMARK PLUS PERFORAT...	Version
Order No.	1540770000	Cutting kit
GTIN (EAN)	4050118345711	
Qty.	1 ST	

THM MULTIMARK TWIN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

M-Print® PRO



The M-Print® PRO printing and ordering software for markers and labels® is a professional Windows®-based solution for both printing and ordering Weidmüller labels and markers . This software allows you to optimise the process of identifying electrical equipment. You can design and order your marking materials easily, professionally and quickly: with text, frames, lines, graphics, bar codes, serial numbers and photos.

- Integrated product catalogue for all labels and markers, incl. images, link to the website and product data sheet
- Markers and labels can be designed on as many levels as required
- Customised formatting of individual text characters (RTF)
- Copy and paste texts and their formats
- Available in 20 languages supporting UNICODE
- Data entry in labels and spreadsheets, or directly in Microsoft Excel
- Creation of scales; numeric and alpha-numeric counters and sequences
- Extensive range of image formats (*.bmp, *.wmf, *.png, *.ico, *.jpeg, *.jpg, *.tif, *.gif)
- Image library including symbols used in electrical engineering
- Product-printer allocation options, e.g. ESG 9/20 to PrintJet; MultiMark on thermotransfer printer
- Online update service via the Internet
- Weidmueller Configurator (WMC) interface
- Import wizard for a number of file formats (*.txt, *.csv, *.xml, etc.) for creating your own import scripts
- Transfer of data from CAE systems
- Permanent print preview: see what the printout will look like even at the design phase, WYSIWYG editing
- Supported output devices: All Weidmueller printers (e.g. PrintJet CONNECT, THM MultiMark, etc.) and standard printers with Microsoft Windows® driver
- Optimal and fast adaptation of output devices
- Multi-level structuring of markers and labels

General ordering data

Type	M-PRINT PRO	Version
Order No.	1905490000	Software for markings, Software, Windows 10, Windows 11, Printer
GTIN (EAN)	4032248526291	software
Qty.	1 ST	