

PVHYM-XXM+XX06M+11**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The Y cable is used for the parallel connection of several strings in a PV system, e.g. for splitting a line in front of an inverter.

The cables are available in different connection variants.

General ordering data

Version	Photovoltaics, Y-Connector Cable, 1x MC4 Male, 2x MC4 Female, 6mm ² , 1100 V
Order No.	3032100000
Type	PVHYM-XXM+XX06M+11
GTIN (EAN)	4099986981164
Qty.	1 items

PVHYM-XXM+XX06M+11

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Dimensions and weights

Net weight

89.8 g

Environmental Product Compliance

RoHS Compliance Status

Compliant

REACH SVHC

No SVHC above 0.1 wt%

PV cable harnessing

PV cable version

Cable side	left
Number	1
Cable length	160 mm
Cable colour	black
Cable cross section	6 mm ²
Rated current	39 A
Inline fuse integrated	No
Version of cable end (In-Block)	connector
Connector version	MC 4
Type of plug-in contact	male
Cable side	right 1
Number	1
Cable length	200 mm
Cable colour	black
Cable cross section	6 mm ²
Rated current	39 A
Inline fuse integrated	No
Version of cable end (In-Block)	connector
Connector version	MC 4
Type of plug-in contact	female
Cable side	right 2
Number	2
Cable length	200 mm
Cable colour	black
Cable cross section	6 mm ²
Rated current	39 A
Inline fuse integrated	No
Version of cable end (In-Block)	connector
Connector version	MC 4
Type of plug-in contact	female

Rated DC voltage

1100 V

Wire cross-section

6.00 mm²

Electrical characteristics

Rated DC voltage

1100 V

PVHYM-XXM+XX06M+11**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 8.0	EC001576	ETIM 9.0	EC001576
ETIM 10.0	EC001576	ECLASS 14.0	27-06-04-02
ECLASS 15.0	27-06-04-02		

PVHYM-XXM+XX06M+11

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



PVHYM-XXM+XX06M+11

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Drawings

www.weidmueller.com

