

**HSS-HF 2.4-4.8 EL W75M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

Version	TwinMark, Conductor and cable markers, 2.4 - 4.8 mm, white
Order No.	<a href="#">2904830000</a>
Type	HSS-HF 2.4-4.8 EL W75M
GTIN (EAN)	4099986685314
Qty.	1 items

## HSS-HF 2.4-4.8 EL W75M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	0.77 mm	Depth (inches)	0.0303 inch
Width	7.6 mm	Width (inches)	0.2992 inch
Length	75000 mm	Length (inches)	2952.75 inch
Net weight	732 g		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Type of printing	neutral	
Width	7.6 mm	
Operating temperature range, max.	105 °C	
Operating temperature range, min.	-55 °C	
Colour	white	
Halogen	No	
Length	75000 mm	
Basic material	Polyolefine	
Printed characters	without	
Number of markers per packaging unit compatible printer	Form of supply	Shrink sleeve reel
Number of markers per combination	1 Shrink sleeve reel = Conductor and cable markers	

### Conductor and cable markers

Halogen	No	Conductor cross-section, max.	4 mm <sup>2</sup>
Conductor cross-section, min.	0.75 mm <sup>2</sup>	Conductor O.D., max.	4.8 mm
Conductor O.D., min.	2.4 mm	Conductor O.D.	2.4 - 4.8 mm
Cross-section for connected wire	0.75 - 4 mm <sup>2</sup>		

### Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

## HSS-HF 2.4-4.8 EL W75M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Accessories

## Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

## General ordering data

Type	RIBBON MM-HS 60/300 SW	Version	
Order No.	<a href="#">2448880000</a>	Ink ribbon	
GTIN (EAN)	4050118462944		
Qty.	1 ST		