


SFC-DS 3/12 MC NE WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**SFC – SlimFix Clip MultiCard with two labelling fields**

For conductor markers, it is often required to quickly read the start and destination designation of the respective conductor. Here it makes sense to print both data directly on a marker.

The new SFC-DS markers are designed as MultiCards and are suitable for direct printing with our PrintJet printing system. Their two labelling areas allow multiple data to be printed on a single marker. The print data can be imported directly from CAE projects into the M-Print® PRO marking software. After printing, the markers are placed around the conductor and securely fixed with a special locking mechanism.

General ordering data

Version	Conductor and cable markers, 12 x 7 mm, white
Order No.	2905150000
Type	SFC-DS 3/12 MC NE WS
GTIN (EAN)	4099986918801
Qty.	120 items

SFC-DS 3/12 MC NE WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	6 mm	Depth (inches)	0.2362 inch
Height	12 mm	Height (inches)	0.4724 inch
Width	7 mm	Width (inches)	0.2756 inch
Net weight	0.56 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.003 kg CO2 eq.	

General data

Type of printing	neutral	Version	with snap-in foot
Width	7 mm	UL 94 flammability rating	V-2, UL 94
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Colour	white	Halogen	No
Basic material	Polyamide 66	Printed characters	without
Size of labelling field	11 x 5 mm	Number per roll	24

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	10 mm ²
Conductor O.D., max.	7 mm	Conductor O.D., min.	4.5 mm
Cross-section for connected wire	10 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

SFC-DS 3/12 MC NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

