

MOPL K21 STAHL
Weidmüller Interface GmbH & Co. KG

 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com
Similar to illustration


Abbildung ähnlich

The system accessories for the Klippon® K enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35 and TS15
- Mounting plates
- Hinges
- Wall-mounted holder

Weidmüller can manufacture and supply this enclosure - according to customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

| | |
|------------|---|
| Version | Klippon K (aluminium empty enclosure), Mounting plate, Mounting plate, Height: 67 mm, Width: 114 mm, Depth: 2 mm, Basic material: Sheet steel, galvanized, galvanized, silver |
| Order No. | 3073020000 |
| Type | MOPL K21 STAHL |
| GTIN (EAN) | 4008190857950 |
| Qty. | 1 items |

MOPL K21 STAHL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|-----------------------------|---------|----------------------------|-------------|
| Depth | 2 mm | Depth (inches) | 0.0787 inch |
| Height | 67 mm | Height (inches) | 2.6378 inch |
| Width | 114 mm | Width (inches) | 4.4882 inch |
| Mounting dimension - height | 33.5 mm | Mounting dimension - width | 106 mm |
| Net weight | 102 g | | |

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General information

| | | | |
|--------------------|------------|----------------|-------------------------|
| Material thickness | 2 mm | Type of fixing | when screwed in |
| Surface finish | galvanized | Basic material | Sheet steel, galvanized |

General information on accessories

| | | | |
|----------------------------|------------|-----------------------------|-------------------------|
| Material thickness | 2 mm | Type of fixing | when screwed in |
| Surface finish | galvanized | Basic material | Sheet steel, galvanized |
| Mounting dimension - width | 106 mm | Mounting dimension - height | 33.5 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000213 | ETIM 9.0 | EC000213 |
| ETIM 10.0 | EC000213 | ECLASS 14.0 | 27-40-06-39 |
| ECLASS 15.0 | 27-40-06-39 | | |