

MOPL K6 STAHL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

The system accessories for the Klippon® K enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35 and TS15
- Mounting plates
- Hinges
- Wall-mounted holder

Weidmüller can manufacture and supply this enclosure - according to customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

| | |
|------------|--|
| Version | Klippon K (aluminium empty enclosure), Mounting plate, Mounting plate, Height: 145 mm, Width: 183 mm, Depth: 2 mm, Basic material: Sheet steel, galvanized, galvanized, silver |
| Order No. | 3073110000 |
| Type | MOPL K6 STAHL |
| GTIN (EAN) | 4008190858049 |
| Qty. | 1 items |

MOPL K6 STAHL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|-----------------------------|---------|----------------------------|-------------|
| Depth | 2 mm | Depth (inches) | 0.0787 inch |
| Height | 145 mm | Height (inches) | 5.7086 inch |
| Width | 183 mm | Width (inches) | 7.2047 inch |
| Mounting dimension - height | 72.5 mm | Mounting dimension - width | 162 mm |
| Net weight | 357 g | | |

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General information

| | | | |
|--------------------|------------|----------------|-------------------------|
| Material thickness | 2 mm | Type of fixing | when screwed in |
| Surface finish | galvanized | Basic material | Sheet steel, galvanized |

General information on accessories

| | | | |
|----------------------------|------------|-----------------------------|-------------------------|
| Material thickness | 2 mm | Type of fixing | when screwed in |
| Surface finish | galvanized | Basic material | Sheet steel, galvanized |
| Mounting dimension - width | 162 mm | Mounting dimension - height | 72.5 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000213 | ETIM 9.0 | EC000213 |
| ETIM 10.0 | EC000213 | ECLASS 14.0 | 27-40-06-39 |
| ECLASS 15.0 | 27-40-06-39 | | |