

## U-OS-PWEB-ES-RT-5000/5

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



PROCON-WEB Embedded System is easy to install on u-OS through the app manager.

To implement the optimal web-based HMI solution, PROCON-WEB Embedded System offers the following features:

- Roles and rights based user management
- Extensive alarming
- predefined controls, such as buttons, sliders, text fields or image areas
- powerful more complex controls, like iframes, charts, tables
- flexible scripting for maximum flexibility
- Historian functionality for storage and visualization of historical data
- connection to the controller via communication driver

### General ordering data

|           |   |
|-----------|---|
| Version   | Visualization software, Platform for runtime system: u-OS compatible devices, Number of process variables, max.: 5000, Number of HMI-devices, max.: 5 |
| Order No. | <a href="#">2942030000</a>  |
| Type      | U-OS-PWEB-ES-RT-5000/5  |
| Qty.      | 1 items   |

**U-OS-PWEB-ES-RT-5000/5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

Net weight 0 g

**Environmental Product Compliance**

RoHS Compliance Status Not affected  
 REACH SVHC No SVHC above 0.1 wt%

**Features of the runtime**

|                             |                     |                           |   |
|-----------------------------|---------------------|---------------------------|---|
| Number of HMI-devices, max. | 5                   | Maximum number of drivers | 1   |
| Projectable by              | PROCON-WEB Designer | Runtime features          | Simple and complex controls, Alarming, Historian, User-Management, Process connection via communication drivers |

**Licence information**

|                  |                  |                                   |                  |
|------------------|------------------|-----------------------------------|------------------|
| Licence coverage | One-time licence | Licence type                      | Software licence |
| Licensing by     | WIBU Ticket ID   | Number of process variables, max. | 5000             |

**System requirements**

|                             |        |                           |        |
|-----------------------------|--------|---------------------------|--------|
| Operating system            | u-OS   | Minimal disk space needed | 0.1 GB |
| Minimal memory (RAM) needed | 0.1 GB |                           |        |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001416    | ETIM 9.0    | EC001416    |
| ETIM 10.0   | EC001416    | ECLASS 14.0 | 27-24-25-02 |
| ECLASS 15.0 | 27-24-25-02 |             |             |