

**WIL-VRGBW-FPPF-XXXX-X465-X**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



**General ordering data**

Order No.	3101690000
Type	<a href="#">WIL-VRGBW-FPPF-XXXX-X465-X</a>
GTIN (EAN)	4099987143141
Qty.	1 items

## WIL-VRGBW-FPPF-XXXX-X465-X

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	10 mm	Depth (inches)	0.3937 inch
Height	10 mm	Height (inches)	0.3937 inch
Width	465 mm	Width (inches)	18.3071 inch
Length	465 mm	Length (inches)	18.3071 inch
Net weight	228 g		

### Temperatures

Operating temperature	-20 - 50°C
-----------------------	------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	37ebc061-1fa2-4387-80af-82299a5c3412

### Cable technical specifications

Cable Material	PUR	Sheathing colour	black
Housing main material	Aluminium	Cable length	5 m

### Connection data

Connection thread	without
-------------------	---------

### Electric data

Rated voltage	≤ 5 V DC	Power	2.1 W
Dimmable	Yes		

### General technical data

Shape of the LED module	Rectangular	Operating life	60.000 h
Protection degree	IP67	Efficiency class (according to EU Directive No. 874/2012)	Not required

### Material data


Housing main material	Aluminium	Encapsulation compound	PUR V0
-----------------------	-----------	------------------------	--------

### Classifications

ETIM 8.0	EC000996	ETIM 9.0	EC000996
ETIM 10.0	EC000996	ECLASS 14.0	27-11-06-35
ECLASS 15.0	27-11-06-35		

Drawings

Drawing



**WIL-VRGBW-FPPF-XXXX-X465-X**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### M8 / M12 mounting clip



Weidmüller offers a wide range of tools and accessories for sensor-actuator cabling.

### General ordering data

Type	SAI-M12-CLIP	Version	
Order No.	<a href="#">1362750000</a>		
GTIN (EAN)	4050118164879		
Qty.	10 ST		