

TCB INL THIRD 1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Inspired by 5S and lean management methods, Weidmüller foam inserts ensure an efficient and tidy workplace. Designed according to a modular principle, they offer many advantages and can be selected according to individual requirements.

General ordering data

Order No.	3155240000
Type	TCB INL THIRD 1
GTIN (EAN)	4099987654630
Qty.	1 items

TCB INL THIRD 1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	50 mm	Depth (inches)	1.9685 inch
Height	390 mm	Height (inches)	15.3543 inch
Width	185 mm	Width (inches)	7.2835 inch
Diameter	0 mm	Net weight	952.76 g

Technical data

Description of article	Foam inlay universal big, empty
------------------------	---------------------------------

Tool chest

Assembly	with tools
----------	------------

Assortments

Diameter	0 mm
----------	------

Classifications

ETIM 8.0	EC011819	ETIM 9.0	EC011819
ETIM 10.0	EC011819	ECLASS 14.0	21-07-04-12
ECLASS 15.0	21-07-04-12		

Accessories

Tools



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

Type	STRIPAX 16	Version	
Order No.	9005610000	Tools, Stripping and cutting tool	
GTIN (EAN)	4008190183875		
Qty.	1 ST		

Crimping tools



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Type	PZ 16	Version	
Order No.	9012600000	Pressing tool, Crimping tool for wire-end ferrules, 6mm ² , 16mm ² ,	
GTIN (EAN)	4008190035440	Indent crimp	
Qty.	1 ST		

Cutting tools



Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

TCB INL THIRD 1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

General ordering data

Type	KT 8	Version	
Order No.	9002650000	Cutting tools, Cutting tool for one-hand operation	
GTIN (EAN)	4008190020163		
Qty.	1 ST		

Tools




- For coaxial cable and round (shielded) data cables from 2.5 to 8mm diameter
- 1-, 2- and 3-level stripping in one operation

General ordering data

Type	CST	Version	
Order No.	9030500000	Tools, Sheathing strippers	
GTIN (EAN)	4008190062293		
Qty.	1 ST		

Accessories / replacement parts



- For coaxial cable and round (shielded) data cables from 2.5 to 8mm diameter
- 1-, 2- and 3-level stripping in one operation

General ordering data

Type	MEKA BR CST	Version	
Order No.	9032010000	Accessories, Cutter cassette	
GTIN (EAN)	4008190135928		
Qty.	1 ST		
Type	MEKA BL CST	Version	
Order No.	9032020000	Accessories, Cutter cassette	
GTIN (EAN)	4008190153236		
Qty.	1 ST		
Type	MEKA RT CST	Version	
Order No.	9032040000	Accessories, Cutter cassette	
GTIN (EAN)	4008190004644		
Qty.	1 ST		